

CF98

CLASS
7.4.4

Price Index



TPE Control Cables

Chainflex® CF98

TPE Energy Chain® Cable, control cable for reduced bend radius, oil-resistant, bio-oil-resistant, PVC-free/halogen-free, UV-resistant, abrasion and tear resistant, low temperature flexibility

Conductor
Extremely highly flexible special alloy

Strain relief
Center core for high tensile stresses

Core
Braiding in layers with extremely short pitch

Outer jacket
Gusset-filling, pressure extruded, halogen-free TPE blend



Clean-room

10.86

Construction

Conductors: Special stranded alloy conductors

Conductor insulation: TPE, thin-walled version

Conductor twisting: Conductors stranded in one layer with especially short pitch length.

Conductor colors: In accordance with DIN 47100.

Outer jacket: TPE: particularly abrasion-resistant, high-flex blend, oil-resistant, coolant-resistant. Silicon-free in compliance with PV 3.10.7 - status 1992. **Color:** dark blue (RAL 5011).

Technical Data:

Minimum bending radius, moving: 4 x outer cable diameter

Minimum bending radius, fixed: 3 x outer cable diameter

Permissible temperature, moving: -31°F to +194°F (-35°C to +90°C)

Permissible temperature, fixed: -40°F to +194°F (-40°C to +90°C)

UV-resistance: High

Oil-resistance: High

Voltage: 300V

Testing voltage: 1500 V

Regulations: CE, RoHS: 2002/95/EC; Please reference the Design Section (Chapter 1) for more information.

Cleanroom: According to ISO Class 1

Typical Applications

- for maximum load requirements at 4 x d
- indoor and outdoor applications
- especially for short, very fast applications with small radii and tight design space
- torsion +/-90° with 3 ft. cable length
- automatic insertion machines. automatic doors, cleanroom, very quick handling, low temperature locations

Part No.	AWG	No. of Conductors and Rated Cross-Section in mm²	Outer Diameter (approx)		Copper Index		Weight	
			in.	(mm)	lbs/mft	(kg/km)	lbs/mft	(kg/km)
CF98-01-02	26	2 x 0.14	.16	(4)	2.7	(4)	7.4	(11)
CF98-01-04	26	4 x 0.14	.20	(5)	5.7	(8.5)	10.8	(16)
CF98-01-08	26	8 x 0.14	.26	(6.5)	10.8	(16)	16.1	(24)
CF98-02-04	24	4 x 0.25	.22	(5.5)	10.8	(16)	20.2	(30)
CF98-02-07	24	7 x 0.25	.26	(6.5)	17.5	(26)	35.6	(53)
CF98-02-08	24	8 x 0.25	.28	(7)	20.2	(30)	40.3	(60)
CF98-03-04	22	4 x 0.34	.22	(5.5)	12.9	(19.0)	23.8	(35.0)
CF98-03-07	22	7 x 0.34	.28	(7)	21.5	(32)	37.0	(55)
CF98-05-04	20	4 x 0.50	.24	(6)	21.0	(31)	27.2	(40)

NOTE: The mentioned external diameters are maximum values.

No Minimum Order • No Cut Charges on up to 10 cuts of the same part number