

PANEL MOUNT INDICATOR, NON-RELAMPABLE

LED TECHNOLOGY

MOUNTING HOLE, Ø 0.380"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
LED 12V SERIES				
WL-6091M1-12V	RED	12V-14V	20mA	100,000
WL-6091M3-12V	AMBER	12V-14V	20mA	100,000
WL-6091M5-12V	GREEN	12V-14V	20mA	100,000
WL-6091M6-12V	BLUE	12V-14V	20mA	100,000
WL-6091M7-12V	YELLOW	12V-14V	20mA	100,000
LED 24V SERIES				
WL-6091M1-24V	RED	24V-28V	20mA	100,000
WL-6091M3-24V	AMBER	24V-28V	20mA	100,000
WL-6091M5-24V	GREEN	24V-28V	20mA	100,000
WL-6091M6-24V	BLUE	24V-28V	20mA	100,000
WL-6091M7-24V	YELLOW	24V-28V	20mA	100,000

NOTES


1. Recommended panel thickness
0.030" to 0.250"
2. 6" leads with 1/2" strip are standard
3. Storage temperature
 T_{STG} : -25°C - +80°C
4. Ambient temperature
 T_A : -20°C - +60°C
5. Voltage tolerance
 V_{OP} : $\pm 10\%$
6. Body material
Nylon, white
7. Lens material
Polycarbonate
8. Bezel material
Stainless steel
9. Wire gauge
18 AWG
10. Gaskets
Buna-N
11. Mounting hardware (nut, lock washer, and gasket) included

CERTIFICATIONS

UL (E340667), RoHS



DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

