


Banana Plugs

174-R820B-EX, 174-R820R-EX

KOBICONN

Banana Plugs



Dimensions: mm (in.)

Mouser Stock No.	Color
174-R820B-EX	Black
174-R820R-EX	Red

SPECIFICATIONS	
Rating:	10A
Insulation Resistance:	500VDC 100M Ω Min.
Dielectric Strength:	1200VAC 1 Minute
Temperature Range:	-20°C ~ +80°C
RoHS Compliant by Exemption	

Date Last Revised: 03/06/07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301110

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

174-R820B-EX, 174-R820R-EX