




JKL LAMP PART NUMBER	COLOR LCD HIGH OUTPUT WHITE	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mA rms)	BRIGHTNESS (CANDELA/m ²)	*RATED LIFE (HRS)
BF23312-24B	x = 0.287 y = 0.284	1100 @ 0°C	618	6 ± 1	50,000 ± 20%	20,000

* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- 0		JKL COMPONENTS CORPORATION							
							TITLE							
							MINIATURE COLD CATHODE FLUORESCENT LAMP							
C	X Y AND BRIGHTNESS RATINGS CHANGE		11/12/08		DRAWN BY L. WENGSTROM		APPV'D BY L.R.		DATE 11/12/08		SIZE A	FSCM NO. 55335	DRAWING NO. BF23312-24B	
B	BRIGHTNESS ±10% TO ±20%		6/13/08											
A	CHANGE + ADDITIONAL DIMENSIONS		3/21/08											
	RELEASE & CANCEL P-0701-05		2/21/07											
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE		RELEASED DATE 2/21/07		REVISION DATE 11/12/08		REV. NO. C	SHEET 1 OF 1