

Tucker ‘Pop’ Blind Rivets - Standard
Aluminium



Manufactured To BS5750 (ISO9002).
Aluminium rivet body with steel, zinc plated mandrel.

2.4mm / 3/32in, Hole Ø 2.5mm

Rivet Body	Max Grip			Price per Pack +
(mm)	(mm)	Pack Qty	Order Code	
2.4 x 3.5	0.8	500	107-700B	— —
2.4 x 5.0	2.4	500	162-3633	— —
2.4 x 7.5	4.8	500	107-702B	— —

3.2mm / 1/8in, Hole Ø 3.3mm

Rivet Body	Max Grip			Price per Pack +
(mm)	(mm)	Pack Qty	Order Code	
3.2 x 4.5	1.6	500	107-710B	— —
3.2 x 6.0	3.2	500	162-3427	— —
3.2 x 8.0	4.8	500	162-3428	— —
3.2 x 9.5	6.4	500	107-713B	— —
3.2 x 11.5	7.9	500	107-714B	— —
3.2 x 13.5	9.5	500	107-715B	— —
3.2 x 15.0	11.1	500	107-716B	— —
3.2 x 17.0	12.7	500	107-717B	— —
3.2 x 24.0	19.8	500	107-718B	— —

4mm / 5/32in, Hole Ø 4.1mm

Rivet Body	Max Grip			Price per Pack +
(mm)	(mm)	Pack Qty	Order Code	
4.0 x 7.0	3.2	500	107-720B	— —
4.0 x 10.5	6.4	500	No Order Code	— —
4.0 x 12.0	7.9	500	107-723B	— —
4.0 x 14.0	9.5	500	107-724B	— —
4.0 x 15.5	11.1	500	107-725B	— —
4.0 x 17.5	12.7	500	107-726B	— —
4.0 x 18.5	13.5	500	107-727	— —
4.0 x 24.5	19.8	500	107-728	— —

4.8mm / 3/16in, Hole Ø 4.9mm

Rivet per Pack	Max Grip			Price Each +
(mm)	(mm)	Pack Qty	Order Code	
4.8 x 7.5	3.2	500	No Order Code	— —
4.8 x 9.0	4.8	500	155-3685	— —
4.8 x 11.0	6.4	500	155-5752	— —
4.8 x 12.5	7.9	500	155-5754	— —

524064