




PCB LAYOUT - COMPONENT VIEW



TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: NYLON 66
FLAMABILITY RATING: UL94-V0
COLOR: WHITE
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: TIN
QUALITY CLASS: 25 MATING CYCLES
PITCH: 4.20MM

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 6 TO 9A

NB CIRCUITS □	2-3 □	4-6 □	7-10 □	12-24
AMPERES ▢	9 ▢	8 ▢	7 ▢	6

WORKING VOLTAGE: 600V AC
INSULATOR RESISTANCE: >1000 MOHM
DIELECTRIC WITHSTANDING VOLTAGE: 1500V AC/MN
CONTACT RESISTANCE: 20 mOHM MAX


SOLDERING
WAVE PROCESS ONLY

PACKAGING
TRAY

DIMENSION
A = 4.20 x (NB. PIN / 2 - 1)
B = 4.20 x (NB. PIN / 2) + 1.30

RoHS Compliant

PROJECTION:



GENERAL TOLERANCE

.X = +/- 0.2

.XX = +/- 0.15



APPROVAL: RJ

UNIT: MM

SCALE:

SHEET: 1/2





DRAW: DXS

DESCRIPTION: 4.20MM MALE DUAL ROW RIGHT ANGLE HEADER WITH MOUNTING FLANGES

WERI PART NO: 6490 xx 21022

SIZE

A4

1		2		3		4		5																																																					
				Note: 1.Dimension: Tray Size:354(L)x260(W)x20(H) (mm) Carton Size:360(L)x270(W)x300(H) (mm) 2.Quantity: 18 Tray/Carton <table><tr><th>Pin.</th><th>Pcs/Tray</th><th>Tray/Carton</th><th>Pcs/Carton</th></tr><tr><td>2</td><td>168</td><td>18</td><td>3024</td></tr><tr><td>4</td><td>128</td><td>18</td><td>2304</td></tr><tr><td>6</td><td>104</td><td>18</td><td>1872</td></tr><tr><td>8</td><td>88</td><td>18</td><td>1584</td></tr><tr><td>10</td><td>80</td><td>18</td><td>1440</td></tr><tr><td>12</td><td>64</td><td>18</td><td>1152</td></tr><tr><td>14</td><td>56</td><td>18</td><td>1008</td></tr><tr><td>16</td><td>56</td><td>18</td><td>1008</td></tr><tr><td>18</td><td>48</td><td>18</td><td>864</td></tr><tr><td>20</td><td>48</td><td>18</td><td>864</td></tr><tr><td>22</td><td>40</td><td>18</td><td>720</td></tr><tr><td>24</td><td>40</td><td>18</td><td>720</td></tr></table>						Pin.	Pcs/Tray	Tray/Carton	Pcs/Carton	2	168	18	3024	4	128	18	2304	6	104	18	1872	8	88	18	1584	10	80	18	1440	12	64	18	1152	14	56	18	1008	16	56	18	1008	18	48	18	864	20	48	18	864	22	40	18	720	24	40	18	720
Pin.	Pcs/Tray	Tray/Carton	Pcs/Carton																																																										
2	168	18	3024																																																										
4	128	18	2304																																																										
6	104	18	1872																																																										
8	88	18	1584																																																										
10	80	18	1440																																																										
12	64	18	1152																																																										
14	56	18	1008																																																										
16	56	18	1008																																																										
18	48	18	864																																																										
20	48	18	864																																																										
22	40	18	720																																																										
24	40	18	720																																																										
																																																													
TRAY 18TRAYS				CARTON																																																									
RoHS Compliant <table><tr><td>G</td><td></td><td></td><td></td></tr><tr><td>F</td><td></td><td></td><td></td></tr><tr><td>E</td><td></td><td></td><td></td></tr><tr><td>D</td><td></td><td></td><td></td></tr><tr><td>C</td><td></td><td></td><td></td></tr><tr><td>B</td><td></td><td></td><td></td></tr><tr><td>A</td><td></td><td></td><td></td></tr><tr><td>REV</td><td>DATE</td><td>FILE</td><td>BY</td></tr></table>				G				F				E				D				C				B				A				REV	DATE	FILE	BY	PROJECTION: 		GENERAL TOLERANCE .X = ± 0.2 .XX = ± 0.15																							
G																																																													
F																																																													
E																																																													
D																																																													
C																																																													
B																																																													
A																																																													
REV	DATE	FILE	BY																																																										
				APPROVAL: RJ		UNIT: MM SCALE: SHEET: 2/2 DRAW: PEARL		DESCRIPTION: 4.20MM MALE DUAL ROW RIGHT ANGLE HEADER WITH MOUNTING FLANGES WERI PART NO: 6490 xx 21022_TPK																																																					
								SIZE A4																																																					