



Quartz Crystal

32,768 kHz

SMD-version

model	KX – 327L
frequency	32,768 kHz
operating temperature	standard -20° ~ +70°C available -40° ~ +85°C (= KX-327LT)
frequency tolerance at +25°C	± 20 ppm
temperature tolerance at -20° ~ +70°C -40° ~ +85°C	-0,042 ppm/°C ² typ
load capacitance C _L	12,5 pF, available 7pF
series resonance R ₁ max.	65k Ohm
aging (first year)	± 3 ppm
shunt capacitance C ₀ typical	0,8 pF
drive level in mW max.	0,001
RoHS	started from date code May, 2005
contents of reel	3000 pcs.
part no.	12.87110 ~ 12.87149

