

## Wiha MicroFinish Handle - Non-Slip Grip

**Wiha MicroFinish handle** has a patented non-slip surface - it won't peel, crack or deteriorate when exposed to petroleum solvents. Oil and moisture flow away from the handle surface for a powerful, non-slip grip. You get maximum force and comfort with dry, oily or wet hands.

Blade Chrome-vanadium-molybdenum, hardened and tempered tool steel, gives exceptional tool life, wear resistance and high torque performance

Exact fit precision ground tips

Through hardened blades & hard chrome finish

Hex bolster & steel strike cap on 533 & 534 series

Safe, high density material, eliminates risk of sharp objects becoming embedded in the handle

MicroFinish Handle with patented non slip surface. Ergonomic handle shape for maximum comfort and exceptional torque transfer



**SHOP**

### 520 Slotted Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

| Item No. | mm   | Inch | mm  | Inch | mm  | Inch | mm  | Inch | lbs | pkg. |
|----------|------|------|-----|------|-----|------|-----|------|-----|------|
| 520 05*  | 4.0  | .157 | 100 | 3.9  | 0.8 | .031 | 211 | 8.3  | .16 | 10   |
| 520 10*  | 4.0  | .157 | 150 | 5.9  | 0.8 | .031 | 261 | 10.3 | .17 | 10   |
| 520 20*  | 5.5  | .216 | 125 | 5.0  | 1.0 | .039 | 236 | 9.3  | .20 | 10   |
| 520 25*  | 5.5  | .216 | 150 | 5.9  | 1.0 | .039 | 261 | 10.3 | .21 | 10   |
| 520 35   | 6.5  | .255 | 150 | 5.9  | 1.2 | .047 | 268 | 10.6 | .28 | 10   |
| 520 40   | 8.0  | .315 | 150 | 5.9  | 1.2 | .047 | 274 | 10.8 | .37 | 10   |
| 520 50   | 10.0 | .393 | 200 | 8.0  | 1.6 | .063 | 324 | 12.8 | .50 | 10   |

\*Cabinet Tips



#52090

#52098

### 520 90 Set 5 Pcs. Slotted & Phillips

Blade CVM steel, hardened, hard chromed.

Wiha-MicroFinish handle, cellulose acetate, impact resistant, non-slip, oil and grease resistant.

| Item No. | mm     | mm  | Size | mm     | lbs. |
|----------|--------|-----|------|--------|------|
| 520 90   | 520 05 | 4.0 | 100  | 521 05 | 1    |
|          | 520 20 | 5.5 | 125  | 521 15 | 2    |
|          | 520 40 | 8.0 | 150  |        |      |

**SHOP**

### 520 98 Set 8 Pcs. Slotted & Phillips

| Item No. | mm     | mm   | Size | mm     | lbs. |
|----------|--------|------|------|--------|------|
| 520 98   | 520 05 | 4.0  | 100  | 521 05 | 1    |
|          | 520 20 | 5.5  | 125  | 521 15 | 2    |
|          | 520 35 | 6.5  | 150  | 521 25 | 3    |
|          | 520 40 | 8.0  | 150  |        |      |
|          | 520 50 | 10.0 | 200  |        |      |



**SHOP**

### 521 Phillips Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

| Item No. | Size | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|------|------|
| 521 05   | 1    | 80  | 3.1  | 191 | 7.5  | .15  | 10   |
| 521 10   | 1    | 200 | 8.0  | 311 | 12.2 | .21  | 10   |
| 521 15   | 2    | 100 | 3.9  | 218 | 8.6  | .26  | 10   |
| 521 20   | 2    | 200 | 8.0  | 318 | 12.5 | .34  | 10   |
| 521 25   | 3    | 150 | 5.9  | 274 | 10.8 | .41  | 10   |



**SHOP**

### 526 1/4" Bit holding Screwdriver, With Wiha-MicroFinish Handle

Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft chrome-vanadium steel, nickel-plated. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.

| Item No. | Size | mm  | Inch | mm  | Inch | lbs. | pkg. |
|----------|------|-----|------|-----|------|------|------|
| 526 50   | 1/4  | 125 | 5.0  | 243 | 9.6  | .24  | 10   |

See additional bit holders on page 198-199



Safe Non-Slip Grip