





Electrical Properties:

Frequency Range: 2.4~2.5 GHz
 Impedance: 50Ω nominal
 VSWR: <2.0:1
 Gain: 2 dBi
 Radiation: Omni
 Polarization: Vertical

Mechanical Properties:

Cable: J100 Low Loss Coax Cable
 Cable Length: L to be Specified in Inches
 Connector: SMA Reverse Polarity Plug
 Material: Polycarbonate(Black)
 Body: Brass with Gold plating
 Connector: -20°C to +65°C
 Operation Temp.: -30°C to +75°C
 Storage Temp.:

TITLE	2.4 GHz External Antenna		Rev. Date	SHEET
	765 Model		12/01/08	1 OF 1
UNIT	DWG. NO.	S765FL-L-AH-2450		
mm(In.)				
SCALE				
none				
NEARSON				

NEARSON