





REV	DESCRIPTION	DET	DATE
D	ITEM 3, 130050 WAS 123188	EL	11/09/11
E	128509C WAS 128619C. ADDED 128487	JJC	08/02/12
F	130322CS WAS 127582; 130326 WAS 126745; ADDED 508511; ADDED VIEW; ADDED .547 & .370 DIMS; ADDED PATENT ETCH	HKS	6/13/13



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
- 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-3 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
- 4 128619C ASSEMBLY CONSISTS OF 128509C COLLET AND 128487 DRAWBAR.
- 5 ETCH "U.S. PATENT #6739170" WHERE SHOWN

F	508511	2	B.H.C.S.	10
	128487	1	DRAWBAR	9
	126748-3	1	UNITIZED DEFLECTOR	8
	128509C	1	COLLET & DRAWBAR ASSY	7
F	130326	1	GUARD	6
	120095	1	DEFLECTOR	5
	122727-1	1	BARBED RETAINER	4
	130050	1	UNITIZED CHUCK JAW	3
F	130322CS	1	TOP GUARD	2
	127109C	1	ANVIL	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH		HUCK INTERNATIONAL, INC., I.S.D 1 CORPORATE DR KINGSTON, NEW YORK 12401	
ITAR/ECCN: EAR99		CLEARANCE NOSE ASSEMBLY -04 MGP STRADDLE	
SCH B#: 8467.99.0190		FINAL ASSY: FOR USE WITH 206-375	
HTS: 8467.99.0190		ENG: MVM CK: DATE: 10/21/04 SCALE: 2:1	
		B	99-3748C