





PortaCrimp Dies

One piece die, held together to prevent mix up & loss. Easily interchangeable crimp dies are kept together with a special pin to simplify handling. Reliable crimping performance is consistent and accurate with a parallel action stroke, good to 50,000 cycles.



431 28 PortaCrimp Die Set For Green & Yellow Insulated Terminals & Splices


Item				
No.	Crimps	AWG	lbs.	Pkg.
431 28	4-6 & 0.1-0.4mm ²	26-22 & 12-10	1.2	1



431 29 PortaCrimp Die Set For Red & Blue Insulated Terminals & Splices


Die set for 22-14 AWG (0.5 - 2.5mm).

Item				
No.	Crimps	AWG	lbs.	Pkg.
431 29	1.5-2.5 & 0.5-1.5mm ²	22-14	1.2	1




431 42 PortaCrimp Die Set For Non-Insulated Terminals, Lugs & Splices

Item				
No.	Crimps	AWG	lbs.	Pkg.
431 42	4-6 & 0.5-2.5mm ²	12-10 & 22-14	1.2	1




431 37 PortaCrimp Die Set For Non-Insulated Terminals, Lugs & Splices

Item				
No.	Crimps	Awg	lbs.	Pkg.
431 37	2.5/1.5/0.75mm ²	14/16/20	1.2	1



431 39 PortaCrimp Die Set For Non-Insulated Terminals, Lugs & Splices


Item				
No.	Crimps	AWG	lbs.	Pkg.
431 39	10/6/4mm ²	8/10/12	1.2	1



431 27 PortaCrimp Wire Ferrules - Insulated & Non-Insulated

Die set for 24-8 AWG (0.25-10mm).


Item				
No.	Crimps	AWG	lbs.	Pkg.
431 27	10/6/4/2.5/1-1.5/.25-.75mm ²	8-24	1.2	1



431 53 PortaCrimp Wire Ferrules - Insulated & Non-Insulated

Die set for 6-4 AWG (16-25mm).

Item				
No.	Crimps	AWG	lbs.	Pkg.
431 53	25 & 16mm ²	6 & 4	1.2	1



431 54 PortaCrimp Wire Ferrules - Insulated & Non-Insulated

Die set for 2-1/0 AWG (35-50mm).

Item				
No.	Crimps	AWG	lbs.	Pkg.
431 54	50 & 35mm ²	1/0 & 2	1.2	1



431 46 PortaCrimp Open Barrel, Non-Insulated Standard Commercial Terminals & Lugs - .250" (6.3mm) Push On Terminals

Item				
No.	Crimp	AWG	lbs.	Pkg.
431 46	4-6/1.5-2.5/0.5-1.0mm ²	22-10	1.2	1