


IEEE 1394 Firewire, 6 Pin Receptacle

KOBICONN

154-FWR80

Dimensions: mm (In.)



Notes

Withstanding Voltage:	DC 500 ±50V
Insulation Resistance:	100 Megohms min.
Contact Resistance:	30 Milliohms max.

SPECIFICATIONS

Part Name	Item	Qty.	Material	Note
Contacts:	3	6	Copper Alloy/ Selective Gold Plated	30μ" Gold Plating 30μ" Terminal for Phosphor Bronze
Housing:	2	1	Thermoplastic	
Shell:	1	1	Copper Alloy/ Tin-Lead Plated over Nickel	

Date Last Revised: 10/18/05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300174

IEEE 1394 Firewire, 6 Pin Receptacle

154-FWR80

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-FWR80](#)