




D


C

B

A



SECTION B-B



SECTION A-A

- 1 NICKEL UNDERPLATE .000050 MIN THK ON ENTIRE CONTACT WITH GOLD .000015 THK ON LOCALIZED PLATE AREA AND BRIGHT TIN-LEAD .000100 MIN THK IN CRIMP AREA
- 2 BRIGHT TIN-LEAD .000100 MIN THK OVER NICKEL UNDERPLATE .000050 MIN THK ON ENTIRE CONTACT
- 3 GOLD FLASH IN PLATED CRIMP AREA, .00015 MIN GOLD ON LOCALIZED PLATE AREA, BOTH OVER .000050 MIN NICKEL ON ENTIRE CONTACT, -OR- GOLD FLASH OVER PALLADIUM-NICKEL, .000015 MIN TOTAL THK ON LOCALIZED PLATE AREA AND GOLD FLASH ON PLATED CRIMP AREA, BOTH OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- 4 GOLD FLASH IN PLATED CRIMP AREA, .00100 MIN TIN IN LOCALIZED PLATE AREA, BOTH OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- 5 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL IN THIS AREA.

	5 3	88976-5
	5 4	88976-4
SUPERSEDED BY 88976-5	1	88976-3
	2	88976-2
	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	.02
3 PLC	±	.005
4 PLC	±	-
ANGLES	±	-
FINISH	SEE TABLE	

MATERIAL
PHOS BRONZE

DWN
P.BERRY
3-21-86

CHK
D.WORTHINGTON
3-24-86

APVD
R. SMITH
3-25-86

PRODUCT SPEC
108-9024

APPLICATION SPEC
114-16015

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

CONTACT, FFC .100CL,
.025 SQ PIN
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=88976

RESTRICTED TO
-

SCALE
NTS

SHEET
1 of 1

REV
P2