



3X 6-32 UNC X (.219) BINDING HEAD COMBINATION TERMINAL SCREW

NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø139 MAX ON 1.000 ± .002 CENTERS
- 2 SWITCH IS SUITABLE FOR USE AT TEMPERATURE OF 280° F CHARACTERISTICS TAKEN AT POINT "A"
- 3 "XD" BRANDED ON BOTH SIDES OF SWITCH AND BOTTOM
- 4

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA	
OPERATING FORCE	-----40 G MAX	CONTACT ARRANGEMENT S P D T	
DIFFERENTIAL TRAVEL	-----:050-.080	L19 15A 125, 250 OR 480 VAC 3/4HP 125 VAC, 1 1/2HP 250 VAC 1/2A 125 VDC, 1/4A 250 VDC L288 L315 L306 16A 250V T85 5E4	
OVERTRAVEL	-----:065 MIN		
RELEASE FORCE	-----:7 G MIN		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BA-1RV54352411-A21](#)