







Loading-Plan:



- Transmission properties in accordance with ISO/IEC 11801:2002: Class D.
- Protection level: IP20
- Temperature range: -40°C ...+70°C



For Information Only
won't be replaced when changed

			All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Maß/Free size tolerances		
				Dat.	Name	Maßstab/Scale 2:1	RJ1 cord, IP20 overmolded, 4xAWG , 1x RJ45 plug, CAT 5				
			Detail.	11.02.08	MS						
			Insp.								
			Stand.								
			HARTING Electronics GmbH & Co. KG				TB 09 45 771 0xxx			Blatt/ page 1/2	
34530			D-32339 ESPELKAMP								
Mod.	Dat.	Name					Sub.				

1				2				3				4				5				6				7				8			
A	Cont. no.	Part number		Type of cable				Dim. a					Cont. no.	Part number		Type of cable				Dim. a				A							
	1	09 45 771 0062		4AWG 22/1 solid				0,5 m					52	09 45 771 0169		4AWG 22/7 trailing				6 m											
	2	09 45 771 0063		4AWG 22/1 solid				1 m					53	09 45 771 0170		4AWG 22/7 trailing				7 m											
	3	09 45 771 0064		4AWG 22/1 solid				1,5 m					54	09 45 771 0171		4AWG 22/7 trailing				8 m											
	4	09 45 771 0065		4AWG 22/1 solid				2 m					55	09 45 771 0172		4AWG 22/7 trailing				9 m											
	5	09 45 771 0066		4AWG 22/1 solid				3 m					56	09 45 771 0173		4AWG 22/7 trailing				10 m											
B	6	09 45 771 0067		4AWG 22/1 solid				4 m					57	09 45 771 0174		4AWG 22/7 trailing				15 m				B							
	7	09 45 771 0068		4AWG 22/1 solid				5 m					58	09 45 771 0175		4AWG 22/7 trailing				20 m											
	8	09 45 771 0069		4AWG 22/1 solid				6 m					59	09 45 771 0176		4AWG 22/7 trailing				30 m											
	9	09 45 771 0070		4AWG 22/1 solid				7 m					60	09 45 771 0177		4AWG 22/7 trailing				40 m											
	10	09 45 771 0071		4AWG 22/1 solid				8 m					61	09 45 771 0178		4AWG 22/7 trailing				50 m											
	11	09 45 771 0072		4AWG 22/1 solid				9 m					62	09 45 771 0179		4AWG 22/7 trailing				60 m											
	12	09 45 771 0073		4AWG 22/1 solid				10 m					63	09 45 771 0180		4AWG 22/7 trailing				70 m											
	13	09 45 771 0074		4AWG 22/1 solid				15 m					64	09 45 771 0181		4AWG 22/7 trailing				80 m											
	14	09 45 771 0075		4AWG 22/1 solid				20 m					65	09 45 771 0182		4AWG 22/7 trailing				90 m											
	15	09 45 771 0076		4AWG 22/1 solid				30 m					66	09 45 771 0183		4AWG 22/7 trailing				100 m											
	16	09 45 771 0077		4AWG 22/1 solid				40 m					67	09 45 771 0100		4AWG 22/7 "outdoor"				0,5 m											
	17	09 45 771 0078		4AWG 22/1 solid				50 m					68	09 45 771 0101		4AWG 22/7 "outdoor"				1 m											
	18	09 45 771 0079		4AWG 22/1 solid				60 m					69	09 45 771 0102		4AWG 22/7 "outdoor"				1,5 m											
	19	09 45 771 0080		4AWG 22/1 solid				70 m					70	09 45 771 0103		4AWG 22/7 "outdoor"				2 m											
	20	09 45 771 0081		4AWG 22/1 solid				80 m					71	09 45 771 0104		4AWG 22/7 "outdoor"				3 m											
C	21	09 45 771 0082		4AWG 22/1 solid				90 m					72	09 45 771 0105		4AWG 22/7 "outdoor"				4 m				C							
	22	09 45 771 0083		4AWG 22/1 solid				100 m					73	09 45 771 0106		4AWG 22/7 "outdoor"				5 m											
	23	09 45 771 0121		4AWG 22/7 stranded				0,5 m					74	09 45 771 0107		4AWG 22/7 "outdoor"				6 m											
	24	09 45 771 0122		4AWG 22/7 stranded				1 m					75	09 45 771 0108		4AWG 22/7 "outdoor"				7 m											
	25	09 45 771 0123		4AWG 22/7 stranded				1,5 m					76	09 45 771 0109		4AWG 22/7 "outdoor"				8 m											
	26	09 45 771 0124		4AWG 22/7 stranded				2 m					77	09 45 771 0110		4AWG 22/7 "outdoor"				9 m											
	27	09 45 771 0125		4AWG 22/7 stranded				3 m					78	09 45 771 0111		4AWG 22/7 "outdoor"				10 m											
	28	09 45 771 0126		4AWG 22/7 stranded				4 m					79	09 45 771 0112		4AWG 22/7 "outdoor"				15 m											
	29	09 45 771 0127		4AWG 22/7 stranded				5 m					80	09 45 771 0113		4AWG 22/7 "outdoor"				20 m											
	30	09 45 771 0128		4AWG 22/7 stranded				6 m					81	09 45 771 0114		4AWG 22/7 "outdoor"				30 m											
D	31	09 45 771 0129		4AWG 22/7 stranded				7 m					82	09 45 771 0115		4AWG 22/7 "outdoor"				40 m				D							
	32	09 45 771 0130		4AWG 22/7 stranded				8 m					83	09 45 771 0116		4AWG 22/7 "outdoor"				50 m											
	33	09 45 771 0131		4AWG 22/7 stranded				9 m					84	09 45 771 0117		4AWG 22/7 "outdoor"				60 m											
	34	09 45 771 0151		4AWG 22/7 stranded				10 m					85	09 45 771 0118		4AWG 22/7 "outdoor"				70 m											
	35	09 45 771 0152		4AWG 22/7 stranded				15 m					86	09 45 771 0119		4AWG 22/7 "outdoor"				80 m											
	36	09 45 771 0153		4AWG 22/7 stranded				20 m					87	09 45 771 0120		4AWG 22/7 "outdoor"				90 m											
	37	09 45 771 0154		4AWG 22/7 stranded				30 m					88	09 45 771 0132		4AWG 22/7 "outdoor"				100 m											
	38	09 45 771 0155		4AWG 22/7 stranded				40 m																							
	39	09 45 771 0156		4AWG 22/7 stranded				50 m																							
	40	09 45 771 0157		4AWG 22/7 stranded				60 m																							
E	41	09 45 771 0158		4AWG 22/7 stranded				70 m																E							
	42	09 45 771 0159		4AWG 22/7 stranded				80 m																							
	43	09 45 771 0160		4AWG 22/7 stranded				90 m																							
	44	09 45 771 0161		4AWG 22/7 stranded				100 m																							
	45	09 45 771 0162		4AWG 22/7 trailing				0.5 m																							
	46	09 45 771 0163		4AWG 22/7 trailing				1 m																							
	47	09 45 771 0164		4AWG 22/7 trailing				1.5 m																							
	48	09 45 771 0165		4AWG 22/7 trailing				2 m																							
	49	09 45 771 0166		4AWG 22/7 trailing				3 m																							
	50	09 45 771 0167		4AWG 22/7 trailing				4 m																							
F	51	09 45 771 0168		4AWG 22/7 trailing				5 m																F							
1				2				3				4				5				6				7				8			

For Information Only
won't be replaced when changed

			All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Maßel Free size tolerances																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																			
												RJl cord, IP20 overmolded, 4xAWG , 1x RJ45 plug, CAT 5																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																
																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																												</