



60 Watt Universal Switching Adapter PSA65U Single Output Series



Features

- High Efficiency
- Class B EMI
- Non-vented/Spill-proof Case
- IEC320 C14 Grounded Input

Applications

- Portable Equipment
- Peripherals
- Notebook Computers
- Networking

Safety Approvals

- cUL/UL
- CE
- TUV
- Meeting Cal. Prop. 65

Mechanical Characteristics

- Length: 150.5mm (5.9in)
- Width: 70.5mm (2.8in)
- Height: 39mm (1.5in)
- Weight: 550g (20oz.)

Output Specifications

Model	DC Output Voltage	Load		Ripple (1) P-P (max.)	Regulation Line & Load
		Min.	Max.		
PSA65U-120	+12V	0A	5A	120mV	±5%
PSA65U-150	+15V	0.1A	4A	150mV	±5%
PSA65U-180	+18V	0A	3.3A	180mV	±5%
PSA65U-240	+24V	0A	2.5A	240mV	±5%

(1) Measured with by-pass capacitors 0.1uf/10uf at output connector terminal and oscilloscope set at 20 Mhz.

PhiHong is not responsible for any error and change. Please consult the factory and visit www.phihong.com for the most up-to-date specifications.

PSA65U Characteristics

WWW.PHIHONG.COM

INPUT:

AC Input Voltage Rating
100 to 240VAC

AC Input Voltage Range
90 to 264VAC

AC Input Frequency
47 to 63Hz

Input Current
1.5A (rms) Max. @ 115VAC
0.8A (rms) Max. @ 230VAC

Leakage Current
3.5mA Max.

Inrush Current (cold)
30A for 115VAC at Max. load
60A for 230VAC at Max. load
(Cold start @ ambient 25°C)

OUTPUT:

Efficiency
80% typical

Hold-up Time
16mS Min. @ 120VAC and Max. load

Over-voltage Protection
>130% over-voltage detection, adapter will be shut down

Over-current Protection

Output equipped with short circuit protection – auto restart

Short Circuit Protection

Output can be shorted without damage

ENVIRONMENTAL:

Temperature

Operation	0 to +40°C
Non-operation	-30 to +70°C

Humidity

Operation	8 to 90%
-----------	----------

Emissions

FCC Class B
EN55022 Class B


Dielectric Withstand (Hi-pot) Test

Primary to Secondary: 3000VAC for 1 minute, 10mA

DC Output Connector

2.1x5.5mm Center Positive Standard

Dimension Diagram Unit: mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phihong:

[PSA65U-150-R](#) [PSA-65U-240](#) [PSA-65U-120](#) [PSA-65U-120PB](#) [PSA-65U-120N](#) [PSA-65U-180](#) [PSA-65U-150](#)
[PSA65U-240-R](#) [PSA65U-180-R](#) [PSA65U-120-R](#)