

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020168](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway Rubber Hand Lamp with 100W, Open End Guard with Reflector, 7.62m (25.0') 16/3 SOOW



Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR85374
UL	E59251
General	
Product Family	Portable Lighting
Series	130102
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Hand Lamps
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678897023
Physical	
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	153.92mm (6.060")
Duty	Industrial
Guard Included	Yes
Guard Type	Open End, Reflector
Height	311.66mm (12.270")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V
Material Info	
Engineering Number	114A163

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130102](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION