



DMOS FETs

SO-14




Part Number	Max. $r_{DS(ON)}$ (Ω)	Max. C_{rss} (pF)	Max. t_{on} (ns)
SD5400CY	70	0.5	2
SD5401CY	70	0.5	2

SOT-143



Part Number	Max. $r_{DS(ON)}$ (Ω)	Max. C_{rss} (pF)	Max. t_{on} (ns)
SST211	75	0.5	2
SST213	75	0.5	2
SST215	75	0.5	2

TO-206AF (TO-72)



Part Number	Max. $r_{DS(ON)}$ (Ω)	Max. C_{rss} (pF)	Max. t_{on} (ns)
SD210DE	45	0.5	2
SD211DE	45	0.5	2
SD212DE	45	0.5	2
SD213DE	70	0.5	2

Part Number	Max. $r_{DS(ON)}$ (Ω)	Max. C_{rss} (pF)	Max. t_{on} (ns)
SD214DE	70	0.5	2
SD215DE	70	0.5	2
SD2100	200	1	2