








Coding-key-chambers 2x

29	09 45 715 1575	8xAWG 27/7, stranded, PUR	ø 6.7	25.000
28	09 45 715 1574	8xAWG 27/7, stranded, PUR	ø 6.7	20.000
27	09 45 715 1573	8xAWG 27/7, stranded, PUR	ø 6.7	15.000
26	09 45 715 1572	8xAWG 27/7, stranded, PUR	ø 6.7	10.000
25	09 45 715 1571	8xAWG 27/7, stranded, PUR	ø 6.7	9.000
24	09 45 715 1570	8xAWG 27/7, stranded, PUR	ø 6.7	8.000
23	09 45 715 1569	8xAWG 27/7, stranded, PUR	ø 6.7	7.000
22	09 45 715 1568	8xAWG 27/7, stranded, PUR	ø 6.7	6.000
21	09 45 715 1567	8xAWG 27/7, stranded, PUR	ø 6.7	5.000
20	09 45 715 1566	8xAWG 27/7, stranded, PUR	ø 6.7	4.000
19	09 45 715 1565	8xAWG 27/7, stranded, PUR	ø 6.7	3.000
18	09 45 715 1564	8xAWG 27/7, stranded, PUR	ø 6.7	2.000
17	09 45 715 1563	8xAWG 27/7, stranded, PUR	ø 6.7	1.500
16	09 45 715 1562	8xAWG 27/7, stranded, PUR	ø 6.7	1.000
15	09 45 715 1561	8xAWG 27/7, stranded, PUR	ø 6.7	500
14	09 45 715 1553	8xAWG 28/7, stranded, PVC	ø 6.6	20.000
13	09 45 715 1552	8xAWG 28/7, stranded, PVC	ø 6.6	15.000
12	09 45 715 1551	8xAWG 28/7, stranded, PVC	ø 6.6	10.000
11	09 45 715 1531	8xAWG 28/7, stranded, PVC	ø 6.6	9.000
10	09 45 715 1530	8xAWG 28/7, stranded, PVC	ø 6.6	8.000
9	09 45 715 1529	8xAWG 28/7, stranded, PVC	ø 6.6	7.000
8	09 45 715 1528	8xAWG 28/7, stranded, PVC	ø 6.6	6.000
7	09 45 715 1527	8xAWG 28/7, stranded, PVC	ø 6.6	5.000
6	09 45 715 1526	8xAWG 28/7, stranded, PVC	ø 6.6	4.000
5	09 45 715 1525	8xAWG 28/7, stranded, PVC	ø 6.6	3.000
4	09 45 715 1524	8xAWG 28/7, stranded, PVC	ø 6.6	2.000
3	09 45 715 1523	8xAWG 28/7, stranded, PVC	ø 6.6	1.500
2	09 45 715 1522	8xAWG 28/7, stranded, PVC	ø 6.6	1.000
1	09 45 715 1521	8xAWG 28/7, stranded, PVC	ø 6.6	500

Cont-No.	Part-No.	Type of cable	Dim. a [mm]	Dim. a [mm]
----------	----------	---------------	-------------	-------------



Transmission properties in accordance with
ISO/IEC 11801:2002: Class E
Protection level: IP67/65
Temperature range: -40°C ...+70°C

All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances	
				Dat.	Name	Maßstab/Scale	
			Detail.	12.01.06	MS	1,4:1	RJ45 Cord, IP67/65, 2xRJ45 Metal-Data3A 8AWG, stranded, CAT6
DRS477A	04.03.09	MS	Insp.	12.01.06	RA	2:1	
35037	04.11.08	MS	Stand.				
34115	11.10.07	MS					
32768							
Mod.	Dat.	Name	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP			TB 09 45 715 15xx	
						Sub.	Blatt/ page

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[09457151563](#) [09457151565](#) [09457151567](#) [09457151572](#) [09457151573](#) [09457151574](#) [09457151575](#)