

speco technologies®

## Color Day/Night Weatherproof Camera



# HT-7715DNV

### Features

- 1/3" SONY ExView\* CCD sensor - 470 lines of resolution • Split Glass Technology to avoid IR reflections
- Auto iris DC Vari-Focal Lens (4mm-9mm)
- LUX level dip switch adjusts day/night settings to your requirements
- Dual voltage operation • Built-in 11 IR LEDs (60' Range\*\*) & CDS sensor for day/night performance
- Controls for BLC, ELC, F/L and L/L • Video Test Connector for easy installation
- Built-in heater extends operating range and avoids condensation • Weatherproof operation
- Excellent low light level performance - 0.03 Lux in existing light, 0.0 Lux with IR LEDs

### Specifications

|                       |                                                              |
|-----------------------|--------------------------------------------------------------|
| Image Sensor          | 1/3" Sony ExView* CCD                                        |
| Resolution            | 470 lines                                                    |
| Minimum Illumination  | .003 lux (IR off) 0.00 lux (IR on)                           |
| Lens                  | DC Auto iris, 4mm-9mm (Varifocal)                            |
| CDS Sensor            | Photoconductive cells - adjustable                           |
| Electronic Shutter    | 1/60 - 1/100,000 seconds                                     |
| Video Output          | 1.0 Vp-p into 75 ohms composite                              |
| TV System             | NTSC                                                         |
| Scanning System       | 2:1 Interlace                                                |
| Sync System           | Line locked/ adjustable V-phase<br>Line lock/internal on-off |
| S/N Ratio             | More than 60 dB                                              |
| Gamma Characteristic  | 0.45                                                         |
| Power Supply          | 24 Volts AC, 12 Volts DC- dual voltage                       |
| Power Consumption     | 600mA                                                        |
| Operating Temperature | -20°F to 122°F - RH 95%                                      |
| Dimensions            | 2.4"W x 2.25"H x 7"L                                         |
| Weight                | 1 lb.                                                        |

\*ExView is a trademark of the Sony Corporation

\*\*Depending on scene reflection

### Package Includes:

HT-7715DNV Camera  
Mounting Hardware

Instructions  
Warranty card

Video Test Cable

Specifications subject to change

For more information contact us at:

Speco Technologies 200 New Highway, Amityville, NY 11701 Web: [www.specotech.com](http://www.specotech.com)  
Toll Free: 1-800-645-5516 In Metro NY: 631-957-8700 Fax: 631-957-9142 or 631-957-3880