

2589-ID-10

NOTES:

- 1. THESE MOUNTING CLIPS ARE FOR HOLDING THE 2481 SERIES HOUSINGS TO THE MAIN PANEL TOPS OF ELECTRIC RANGES.
- 2. SCREW SIZE INDICATION.
- 3. .015/(.38) MAXIMUM CUT OFF.
- 4. .010/(.25) MAXIMUM MISMATCH.
- 5. THREAD FORM FOR A #10-32 SCREW.
- 6. THIS SURFACE MAY BE FORMED IN THIS DIRECTION A MAXIMUM OF 5°.

MATERIAL:

STEEL, STAINLESS, TYPE 301, .020/(.5) THICK.


AC	OBSOLETED P/N UCR2002-0255 01/9/12 COMERC
AB2	REMOVED NOTCH UCR2000-0104 8/11/99 COMERC
AB1	REV. RADII UCR2000-0086 8/05/99 COMERC
AB	REVISED UCR 1999-0818 6/03/99 ELHAG
AA	REVISED ECN U4 0744 6/16/94 RHR
Z	REVISED ECN U4 0213 2/14/94 RHR
Y	REVISED ECN U3 0739 5/13/93 RHR
X	REDRAWN & REDIM. ECN U2 1712 11/25/92 RHR

3	AB	
2	Z	
1	AC	X
MFG.	SH.	REV.
LTR.		REVISIONS

DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES ANGULAR ± .006 5°		TITLE MOUNTING CLIP	
3 PLACE ± .010 --- 2 PLACE ± .014 ± 0.25 1 PLACE --- ± 0.35		PART NO. SD2589X1 DRWG. NO. SD-2589-*	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NO. 1 of 3 DATE 11/20/92	
DRWG. BY RHR CHK'D BY ESS APP'D BY RAS	SCALE 2: 1	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	



I3	I2	I1	I0	9	8	7	6	2589	4	3	2	I
----	----	----	----	---	---	---	---	------	---	---	---	---

	PART NO.	ENG. NO.	DIMENSION	
			A	
J	089-00-2006	2589-ID-10	.48±.025 (12.2±.64)	
	089-00-2022	2589-2C	.53±.025 (13.5±.64)	
	089-00-2025	2589-2H	.656±.025 (16.66±.64)	
I	089-00-2027	2589-2J-10	.562±.025 (14.27±.64)	
	089-00-2041	2589-3B	.48±.025 (12.2±.64)	
	089-00-2047	2589-6F	.375±.015 (9.53±.38)	
H	089-00-2100	2589-10C	.48±.025 (12.2±.64)	
	089-00-2101	2589-21A	.62±.025 (15.7±.64)	OBSOLETE
	089-00-2103	2589-23	.62±.025 (15.7±.64)	




FOR THE REMAINDER
OF DIMENSIONS AND
DETAILS SEE SHEET I

2589-23



FOR THE REMAINDER
OF DIMENSIONS AND
DETAILS SEE SHEET I

2589-21A OBSOLETE



		AA	SEE SHEET I	DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 5°		▽ = 0 ▽ = 0		REVISE ONLY ON CAD SYSTEM															
		Z	SEE SHEET I	<table><tr><th colspan="2">INCH</th><th>METRIC</th></tr><tr><td>3 PLACE</td><td>± .010</td><td>---</td></tr><tr><td>2 PLACE</td><td>± .014</td><td>± 0.25</td></tr><tr><td>1 PLACE</td><td>---</td><td>± 0.35</td></tr></table>		INCH		METRIC	3 PLACE	± .010	---	2 PLACE	± .014	± 0.25	1 PLACE	---	± 0.35	TITLE		MOUNTING CLIP			
INCH		METRIC																					
3 PLACE	± .010	---																					
2 PLACE	± .014	± 0.25																					
1 PLACE	---	± 0.35																					
AB		SEE SHEET I	X	SEE SHEET I	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MOLEX INCORPORATED LITTLE ROCK, AR 68532 U.S.A.		SHEET NO. 3	DATE 2/24/93													
					DRWG. NO. SD-2589- SEE CHART		DRWG. NO. SD-2589-•																
LTR.	REVISIONS	LTR.	REVISIONS	APP'D BY: RAS SCALE: 2: 1		FILE NAME: SD2589X3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		DIV. CP	SIZE C												
				DRWG. BY: RHR CHK'D BY: ESS																			