

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1816028

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
ROSEMONT, ILLINOIS

FED. MFR. CODE 91929

SWITCH-BASIC

CATALOG LISTING

ISEI-3

ISEI-3

PAGE 1 OF 1

M

DRAWING
NUMBER

8

11

ISSUE

8

REVISIONS

A CO-16449

D A W,
28 DEC 61

B CO-34213

J A L
24 SEPT 74

C CO
51463-D

WJM
16 JUL 82

D CO-570414

CJH
21 MAR 85

E CO94274

DLM
MAR 99

FORMTEK

CO-50378

(M) ISEI-3
ISSUE 6

REPLACES

RELEASE NO.


CHECK

CHECK

27 FEB 82

CHECK

D A W 28 DEC 61



NOTE -

- ① MOUNTING HOLES WILL ACCEPT $.087$ MAX DIA PINS OR SCREWS ON $.375 \pm .002$ CENTERS
- ② ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- ③ WEIGHT OF SWITCH ONLY IS $.26$ OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS 1.40 OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 5-17 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 4 OZ MIN	250 VAC ----- 5 AMP	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
RELEASE TRAVEL ----- .004 MIN	30 VOLTS DC RATING	TOLERANCES ARE:
DIFFERENTIAL TRAVEL ----- .004 MAX	INDUCTIVE ----- SEA LEVEL ----- 3 AMP	ONE PLACE (.0) $\pm .030$
OVERTRAVEL ----- .003 MIN	50,000 FT ----- 2.5 AMP	TWO PLACE (.00) $\pm .015$
	RESISTIVE ----- SEA LEVEL ----- 5 AMP	THREE PLACE (.000) $\pm .005$
	50,000 FT ----- 5 AMP	ANGLES $\pm$
	MAXIMUM INRUSH ----- 24 AMP	WEIGHT ③