


DM Series

6.5"~19" IP 65 industrial monitors, Robust, Shock Resistance and OSD Function

Features

1. Aluminum front panel meets IP65 standard for tough working environment
2. Optional RS-232 interface touch screen
3. Robust chassis and retention kit structure for shocking and vibration requirement
4. Over 300cd/m² high brightness and 50000hrs MTFB long lifetime panel
5. Analog VGA interface supports most of general system boards
6. M models support 9~36V DC power input for mobile application



Model	DM-65GS	DM-84GHS-R12	DM-104GHS-R12	DM-121GS-R11	DM-150GS-R11	DM-170GS-R11	DM-190GS-R11	
LCD Size	6.5"	8.4"	10.4"	12.1"	15"	17"	19"	
Input Interface	Analog VGA	Analog VGA	Analog VGA	Analog VGA + DVI-D				
Max Resolution	640 x 480	800 x 600	800 x 600	800 x 600/ 1024 x 768	1024 x 768	1280 x 1024	1280 x 1024	
Brightness (cd/m ²)	400 / 500	400	400	400 / 450	350	300	300	
Contrast Ratio	550 : 1	450 : 1	500 : 1	500 : 1 / 700 : 1	400:1	500:1	700:1	
Display Color	262K	262K	262K	262K	262K	16.2M	16.2M	
Pixel Pitch (mm)	0.207	0.213	0.264	0.3075 / 0.240	0.297	0.264	0.294	
Front Frame	Aluminum							
Chassis	Heavy-duty steel	Heavy-duty steel						
View Angle (H/V)	140/120	120/100	120/100	140/110	160/160	120/100	140/130	140/130
Input Voltage	12VDC	12VDC or 9-36VDC						
OSD function	Yes	Yes	Yes	Yes	Yes	Yes	Yes	
Smart OSD	Yes							
Mounting	Wall/Arm/Din/ Panel/Rack	Wall/Panel/Rack/Arm (100x100)/Stand						
Color	Silver							
Dimension (W x H x D mm)	183 x 143 x 41	244 x 178 x 49	312 x 242 x 53	340 x 260 x 58	410 x 309 x 55.1	452.0 x 356.0 x 65.2	482 x 399 x 73	
Operating Temperature	0~50°C							
Front Panel Protection	IP65							
Net Weight	1 kg	1.8 kgs	3 kgs	3.8 kgs	6 kgs	8.6 kgs	10 kgs	
Power Adapter	25W, 63000-UP0251E12PL02-RS			45W, 63000-UP0451E12P81L-RS				

Mounting Kits Information

	DM-65GS	DM-84GS	DM-104GS	DM-121GS	DM-150GS	DM-170GS	DM-190GS
Panel Mount Kits	PK-65M	PK-84M	PK-104M	PK-170M			PK-190M
Wall Mount Kits	WK-065MS-R10		WK-190MS-R10				
Rack Mount Kits	RK-065MS-R10	RK-084MS-R10	RK-104MS-R10	RK-121MS-R10	RK-150MS-R10	RK-170MS-R10	RK-190MS-R10
Din Mount Kits	DK-84MS			N/A			
LCD Monitor Arm	ARM-11				ARM-31		
LCD Monitor Stand	STAND-100-RS/STAND-150-RS				STAND-210-RS		

Packing List

Description	Remark
1 x AC Power Cable	
1 x VGA Cable	
1 x 45W AC Power Adapter	For DM-121GS / 150GS / 170GS / 190GS series
1 x 25W AC Power Adapter	For DM-65GS / 84GS / 104GS series
1 x User Manual	
1 x Power Cable for Terminal Block	For M model ONLY
1 x Touch Screen RS-232 Cable / Touch Pen / Driver CDROM	For T-R model
1 x Touch Screen USB Cable / Touch Pen / Driver CDROM	For USB/T-R model

Ordering Information

Note: The smartOSD function is only supported by revision 11 models and above

Part No.	Description
6.5"	DM-65GS/T-R 6.5" 400cd/m ² VGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, RoHS
	DM-65GHS/T-R 6.5" 500cd/m ² High Luminance VGA LCD Monitor with VGA, Aluminum Front Panel, Silver Color, W/8.4" Touch Screen, RoHS
8.4"	DM-84GHS-R12/T-R 8.4" 400cd/m ² High Luminance SVGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, RoHS
	DM-84GHMS-R12/T-R 8.4" 400cd/m ² High Luminance SVGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, 9~36V DC input, RoHS
10.4"	DM-104GHS-R12/T-R 10.4" 400cd/m ² High Luminance SVGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, RoHS
	DM-104GHMS-R12/T-R 10.4" 400cd/m ² High Luminance SVGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, 9~36V DC input, RoHS
12.1"	DM-121GS-R11/T-R 12.1" 400cd/m ² SVGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, RoHS
	DM-121GMS-R11/T-R 12.1" 400cd/m ² SVGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, 9~36V DC input, RoHS
	DM-121GS-USB-R11/T-R 12.1" 400cd/m ² SVGA LCD Monitor, Aluminum Front Panel, Silver Color, W/12.1" USB Touch Screen, RoHS
	DM-121GMS-USB-R11/T-R 12.1" 400cd/m ² SVGA LCD Monitor, Aluminum Front Panel, Silver Color, W/12.1" USB Touch Screen, 9~36V DC input, RoHS
	DM-121GXS-R11/T-R 12.1" 450cd/m ² XGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, RoHS
	DM-121GXMS-R11/T-R 12.1" 450cd/m ² XGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, 9~36V DC input, RoHS
	DM-121GXS-USB-R11/T-R 12.1" 450cd/m ² XGA LCD Monitor, Aluminum Front Panel, Silver Color, W/12.1" USB Touch Screen, RoHS
	DM-121GXMS-USB-R11/T-R 12.1" 450cd/m ² XGA LCD Monitor, Aluminum Front Panel, Silver Color, W/12.1" USB Touch Screen, 9~36V DC input, RoHS
15"	DM-150GS-R11/T-R 15" 350cd/m ² XGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, RoHS
	DM-150GMS-R11/T-R 15" 350cd/m ² XGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, 9~36V DC input, RoHS
	DM-150GS-USB-R11/T-R 15" 350cd/m ² XGA LCD Monitor, Aluminum Front Panel, Silver Color, W/15" USB Touch Screen, RoHS
	DM-150GMS-USB-R11/T-R 15" 350cd/m ² XGA LCD Monitor, Aluminum Front Panel, Silver Color, W/15" USB Touch Screen, 9~36V DC input, RoHS
17"	DM-170GS-R11/T-R 17" 300cd/m ² SXGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, RoHS
	DM-170GMS-R11/T-R 17" 300cd/m ² SXGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, 9~36V DC input, RoHS
	DM-170GS-USB-R11/T-R 17" 300cd/m ² SXGA LCD Monitor, Aluminum Front Panel, Silver Color, W/17" USB Touch Screen, RoHS
	DM-170GMS-USB-R11/T-R 17" 300cd/m ² SXGA LCD Monitor, Aluminum Front Panel, Silver Color, W/17" USB Touch Screen, 9~36V DC input, RoHS
19"	DM-190GS-R11/T-R 19" 300cd/m ² SXGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, RoHS
	DM-190GMS-R11/T-R 19" 300cd/m ² SXGA LCD Monitor, Aluminum Front Panel, Silver Color, W / Touch Screen, 9~36V DC input, RoHS
	DM-190GS-USB-R11/T-R 19" 300cd/m ² SXGA LCD Monitor, Aluminum Front Panel, Silver Color, W/19" USB Touch Screen, RoHS 7
	DM-190GMS-USB-R11/T-R 19" 300cd/m ² SXGA LCD Monitor, Aluminum Front Panel, Silver Color, W/19" USB Touch Screen, 9~36V DC input, RoHS

