



G1238 series



Size: (120 x 120 x 38 mm)
4.69 x 4.69 x 1.5 inches

Features: *brass bearing stand*
Construction: UL94V-0 PBT impeller & frame
Bearing option: ball bearing
Connection: AWG 24,1007 lead wires
Frame: flanged
Protection: thermal
Options: tachometer output or locked rotor alarm signal; encapsulated motor



Model No.	Rated Voltage V	Current mA			Revolution RPM	Air Volume		Max. Static Pressure (H ₂ O)		Sound Noise dbA	Weight g
		12	24	48		M³/Min.	CFM	MM	INCH		
G1238S	12/24/48	250	180	80	2,000	2.50	88	4.39	0.17	34	262
G1238L	12/24/48	400	250	130	2,400	3.03	107	6.22	0.24	38	262
G1238M	12/24/48	600	330	180	2,800	3.54	125	8.16	0.32	43	262
G1238H	12/24/48	750	450	250	3,200	3.99	141	10.31	0.41	46	262
G1238E	12/24/48	1200	600	330	3,600	4.46	158	12.45	0.49	49	262