





MATERIALS

1. HOUSING : P.B.T. (UL 94V-0), BLACK.
2. TERMINAL : S.Q. 0.64mm GOLD PLATING.

SPECIFICATION

1. CURRENT RATING : 3 AMP. MAX.
2. DIELECTRIC WITHSTANDING VOLTAGE : 1000V AC R.M.S. FOR ONE MINUTE.
3. INSULATION RESISTANCE : 5000M OHMS MIN. AT 1000V DC.
4. OPERATING TEMPERATURE : -55°C TO +105°C.

Dimensions

Pos.	A	B	C
10	32.00	27.94	10.16
14	37.08	33.02	15.24
16	39.62	35.56	17.78
20	44.70	40.64	22.86
24	49.78	45.72	27.94
26	52.32	48.26	30.48
30	57.40	53.34	35.56
34	62.48	58.42	40.64
40	70.10	66.04	48.26
50	82.80	78.74	60.96

玄茂科技股份有限公司
HSUAN MAO TECHNOLOGY CO., LTD.

制表日: 2006/01/10

DRAWING.

Jolin

APPROVED

UNIT

MM

APPD.

CKD.

SCALE

TOLERANCE

PART NAME

2.54x2.54mm FULLY SHROUDED
HEADER 180° LONG LATCH

PART NO.

C3000-XXSLXB00R

REV.

A