


HEYCO



Heyco® Rubber Grommets

For Panels .125" (3,2 mm) to .188" (4,8 mm) Thick

- **Used to protect through holes.**
Help eliminate sharp edges so your wires are protected and add aesthetic value to your application.
- 113 sizes available that will accommodate mounting holes ranging from .250" (6,4 mm) to holes as large as 2.375" (60,3 mm) diameter and panel thicknesses from .063" (1,6 mm) to .188" (4,8 mm).
- Rubber grommets are constructed of SBR (unless otherwise noted) with an operating temperature range of -40°F (-40°C) to 221°F (105°C).
- SBR grommets have good water resistant characteristics and are suitable for most moderate chemicals and wet or dry organic acids.
- Provide vibration dampening.



MOUNTING HOLE DIAMETER		PART NO.	DESCRIPTION	MATERIAL	PART DIMENSIONS					
					A Inside Diameter		B Head Diameter		C Overall Height	
in.	mm.	Black			in.	mm.	in.	mm.	in.	mm.
For .125" (3,2 mm) Thick Panels (continued)										
1.375	34,9	G1322	RG 1375-32-4	SBR	1.000	25,4	1.750	44,5	.500	12,7
1.500	38,1	G1350	RG 1500-40-4	SBR	1.250	31,8	1.875	47,6	.406	10,3
1.625	41,3	G1363	RG 1625-42-4	SBR	1.313	33,4	2.000	50,8	.438	11,1
		G1364	RG 1625-44-4	SBR	1.375	34,9	1.875	47,6	.406	10,3
1.750	44,5	G1371	RG 1750-48-4	SBR	1.500	38,1	2.125	54,0	.500	12,7
2.000	50,8	G1392	RG 2000-56-4	SBR	1.750	44,5	2.375	60,3	.375	9,5
2.500	63,5	G1423	RG 2.5-68-4	SBR	2.125	54,0	2.875	73,0	.438	11,1
For .156" (4,0 mm) Thick Panels										
.500	12,7	G1094	RG 500-12-5	SBR	.375	9,5	.688	17,5	.313	8,0
.750	19,1	G1181	RG 750-16-5	SBR	.500	12,7	.938	23,8	.406	10,3
1.500	38,1	G1348	RG 1500-38-5	SBR	1.188	30,2	1.750	44,5	.406	10,3
For .188" (4,8 mm) Thick Panels										
.312	7,9	G1022	RG 312-6-6	SBR	.188	4,8	.438	11,8	.313	8,0
.375	9,5	G1034	RG 375-6-6	SBR	.188	4,8	.625	15,9	.375	9,5
.437	11,1	G1057	RG 437-8-6	SBR	.250	6,4	.625	15,9	.313	8,0
.562	14,3	G1110	RG 562-6-6	Nitrile	.188	4,8	.750	19,1	.313	8,0
		G1115	RG 562-10-6	SBR	.313	8,0	.813	20,7	.375	9,5
		G1116	RG 562-10-6A	SBR	.313	8,0	.813	20,7	.438	11,1
		G1120	RG 562-12-6	SBR	.375	9,5	.813	20,7	.375	9,5
.625	15,9	G1133	RG 625-12-6	SBR	.375	9,5	.875	22,2	.438	11,1
		G1135	RG 625-13-6	Nitrile	.400	10,2	1.100	27,9		
.687	17,5	G1153	RG 687-14-6	SBR	.438	11,1	.938	23,8	.438	11,1
.750	19,1	G1172	RG 750-10-6	SBR	.313	8,0	1.000	25,4	.438	11,1
.812	20,6	G1194	RG 812-16-6	SBR	.500	12,7	1.063	27,0	.438	11,1
		G1199	RG 812-18-6	SBR	.563	14,3				
.875	22,2	G1213	RG 875-18-6	SBR	.563	14,3	1.063	27,0	.438	11,1
		G1219	RG 875-20-6	SBR	.625	15,9	1.125	28,6		
1.000	25,4	G1256	RG 1000-22-6	SBR	.688	17,5	1.313	33,4	.500	12,7
		G1261	RG 1000-24-6	SBR	.750	19,1	1.250	31,8	.563	14,3
1.062	27,0	G1272	RG 1062-24-6	SBR	.750	19,1	1.375	34,9	.500	12,7
1.250	31,8	G1306	RG 1250-28-6	SBR	.875	22,2	1.625	41,3	.563	14,3
		G1312	RG 1250-32-6	SBR	1.000	25,4	1.500	38,1	.438	11,1
1.375	34,9	G1323	RG 1375-32-6	SBR	1.000	25,4	1.750	44,5	.563	14,3
		G1329	RG 1375-36-6	SBR	1.125	28,6	1.875	47,6	.500	12,7
1.500	38,1	G1351	RG 1500-40-6	EPDM	1.250	31,8	2.000	50,8	.625	15,9
1.750	44,5	G1372	RG 1750-48-6	SBR	1.500	38,1	2.125	54,0	.563	14,3
2.000	50,8	G1390	RG 2000-52-6	SBR	1.625	41,3	2.250	57,2	.750	19,1
2.200	55,9	G1404	RG 2.200-64-6	SBR	2.000	50,8	2.750	69,9	.560	14,2
2.375	60,3	G1414	RG 2.375-64-6	PVC	2.000	50,8	2.750	69,9	.560	14,2

Standard color black.

Quick Specs

Material
Temperature Rating

SBR, Nitrile, EPDM, or PVC
-40°F (-40°C) to 221°F (105°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[G1351](#) [G1135](#) [G1272](#) [G1329](#) [G1404](#) [G1219](#) [G1256](#) [G1392](#) [G1153](#) [G1022](#) [G1199](#) [G1181](#) [G1172](#) [G1306](#)
[G1364](#) [G1371](#) [G1213](#) [G1372](#) [G1116](#) [G1414](#) [G1348](#) [G1322](#) [G1110](#) [G1034](#) [G1057](#) [G1115](#) [G1194](#) [G1350](#)
[G1094](#) [G1120](#) [G1363](#) [G1261](#) [G1133](#) [G1423](#) [G1390](#) [G1323](#) [G1312](#)