










1274-SL





1274T-SL



Loose Part No.	1092	1274
Reeled Part No.	6092	6274
Taped Part No.	1092T	1092T-KT
Mating Terminal Size	0.025" (0.64mm) and 0.032" (0.81mm)	0.020" (0.51mm) and 0.032" (0.81mm)
Mounting Type	Split Leg Inward Splay	
Material Thickness / Type	0.016" (0.41mm) C26000 Brass	
Standard Finish	100% Matte Tin over Copper (0)	
Mating Entry	Top and Horizontal	
Mounting Hole Diameter	2 holes 0.066" ± 0.003" (1.68mm ± 0.076mm) on 0.134" ± 0.003" (3.40mm ± 0.076mm) centers	
Current Rating	20 Amperes	
Resistance Rating	10mOhm Max	
Temperature Rating	-65° to 85°C	
Applicator System	Loose: ZPT81-1092 Reeled: Model 9700, 9700 XY	

