

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200790239

Status:

Active

Overview:


Brad Ultra-Lock Connection System

Description:

Ultra-Lock (M12) Single-Ended Cordset, 5 Poles, Male (90°) to Pigtail, 22 AWG, PVC Cable, 2.0m (6.56') Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
General	
Product Family	Industrial Cordsets
Series	120079
Connector End A	Ultra-Lock (M12)
Connector End B	Pigtail
IP Rating	IP69K
Material - Contact	Copper Alloy
Overview	Brad Ultra-Lock Connection System
Product Name	Ultra-Lock (M12)
Protocol	EtherNet
Region	America
Type	Single Ended
UPC	78678884704
Physical	
Cable Diameter	5.72mm (.225")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Coupling Style	Push to Lock
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	22
Wire/Cable Type	UL 2661
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	W05007A09M020
Reference - Drawing Numbers	
Sales Drawing	SD-120079-008



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
120079 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION