



NYS373-*

Phono plug, black shell, gold plated contacts, rubber boot for best antikink protection, chuck type strain relief for cable O.D. 3.5 to 6.1 mm, color coding ring

*: 0-Black, 2-Red, 4-Yellow, 5-Green, 6-Blue, 9-White



Image gallery



Technical Information

[hide](#)

Product

Title	NYS373-*
-------	----------

Electrical

Dielectric strength	0.5 kVdc
---------------------	----------

Insulation resistance	$\geq 1 \text{ G}\Omega$
-----------------------	--------------------------

Rated current	depends on mated connector
---------------	----------------------------

Contact resistance	depends on mated connector
--------------------	----------------------------

Mechanical	
Cable O.D.	3.5 - 6.1 mm
Lifetime	> 1000 mating cycles
Wiresize	24 AWG
Material	
Contact plating	Au
Contacts	Brass (CuZn39Pb3)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black
Strain relief	Internal plastic chuck
Insulation	Thermoplastic
Environmental	
Solderability	Complies with IEC 68-2-20
Temperature range	-25 °C to +70 °C