





LOC		DIST		REVISIONS									
AD		25		P	F	ZONE	LTR	DESCRIPTION				DATE	APPD
							E	EC 0010-1434-95				1/18/96	RAP
							F	EC 0010-1486-95				4/1/96	CR
							G	REV PER EC 001B-0367-00				04 JAN 01	CR

- 1
- HOUSING MATERIAL: GLASS-FILLED POLYESTER. COLOR: GRAY.
- 2
- CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3
- CONTACT FINISH: 0.00076[.000030] GOLD IN CONTACT AREA. 0.00127[.000050] NICKEL UNDERPLATE ALL OVER. TIN-LEAD ON POSTS.
- 4
- PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO IN THIS APPROXIMATE AREA.
- 5
- POINT OF MEASUREMENT FOR GOLD.
- 6
- ACTION PIN POSTS REQUIRE 1.57[.062] MIN THICK PC BOARD. RECOMMENDED PC BOARD HOLES ARE Ø1.151±0.02[.0453±.001] DRILLED HOLE WITH 0.02-0.07[.001-.003] COPPER AND 0.008[.0003] MIN TIN-LEAD PLATING. FINISHED HOLE AFTER PLATING, Ø0.94-1.09[.037-.043].
- 7
- CONTACT FINISH: DIN 41612 CLASS 3 IN CONTACT AREA. 0.00127[.000050] NICKEL UNDERPLATE ALL OVER. TIN-LEAD ON TAILS.
- 8
- CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. 0.00127[.000050] NICKEL UNDERPLATE ALL OVER. TIN-LEAD ON TAILS.



OBSOLETE		7	1 THRU 40	X	X	X	120	535079-9		
SUPERSEDED BY 535079-5		8	1 THRU 40	X	X	X	120	535079-5		
		3	1 THRU 40	X	X	X	120	535079-4		
		NOTES		POSITIONS LOADED		C	B	A	NO. OF LOADED POSITION	ASSY PART NUMBER
						ROWS LOADED				
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 1 PLC DEC ± - 2 PLC DEC ± 0.13[.005] ANGLES ± -		DR		5/11/89		AMP INCORPORATED Harrisburg, Pa. 17105				
		L. BRINER								
		CHK		6/26/89						
		J. BROWN								
		APPD		6/26/89						
MATERIAL		J. BROWN				NAME ASSEMBLY, RECEPTACLE, EUROCARD, TOOLLESS PRESSFIT, 120 POSITION				
		APPD		6/26/89						
		J. BROWN								
HSG 1		APPD		6/26/89						
		J. BROWN								
CONT 2		PRODUCT SPEC		-						
FINISH		APPLICATION SPEC		-		SIZE	FSCM NO		DRAWING NO	
CONT 3 7 8				-		D	00779		535079	
		WEIGHT		-		SCALE		4:1		SHEET