



13			12		11		10		9		8		7		6		5		4		3		2		1			
PACKAGING SEE NOTE 4 SHT 1			4-6 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		BULK			
			8-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TUBES			
			DIM. M ±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)				8.13 (.320)					
			PLATING				150 TIN				15 GOLD				30 GOLD				15 GOLD				30 GOLD					
DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)				4.57 (.180)								
DIM. A			DIM. B		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		CKTS	
MM		IN	MM	IN	015-91-2040		015-91-6040		N/A		015-91-0040		015-91-6042		N/A		015-91-3040		015-91-6043		N/A		015-91-0048		015-91-5049		04	
06 7.62		.300	5.08	.200	015-91-2060		015-91-6060		N/A		015-91-0060		015-91-6062		N/A		015-91-3060		015-91-6063		N/A		015-91-0068		015-91-5069		06	
08 10.16		.400	7.62	.300	015-91-2080		015-91-6080		015-91-3087		015-91-0080		015-91-6082		015-91-3086		015-91-3080		015-91-6083		015-91-3088		015-91-0088		015-91-5089		08	
10 12.70		.500	10.16	.400	015-91-2100		015-91-6100		015-91-3107		015-91-0100		015-91-6102		015-91-3106		015-91-3100		015-91-6103		015-91-3108		015-91-0108		015-91-5109		10	
12 15.24		.600	12.70	.500	015-91-2120		015-91-6120		015-91-3127		015-91-0120		015-91-6122		015-91-3126		015-91-3120		015-91-6123		015-91-3128		015-91-0128		015-91-5129		12	
14 17.78		.700	15.24	.600	015-91-2140		015-91-6140		015-91-3147		015-91-0140		015-91-6142		015-91-3146		015-91-3140		015-91-6143		015-91-3148		015-91-0148		015-91-5149		14	
16 20.32		.800	17.78	.700	015-91-2160		015-91-6160		015-91-3167		015-91-0160		015-91-6162		015-91-3166		015-91-3160		015-91-6163		015-91-3168		015-91-0168		015-91-5169		16	
18 22.86		.900	20.32	.800	015-91-2180				015-91-3187		015-91-0180				015-91-3186		015-91-3180				015-91-3188		015-91-0188		015-91-5189		18	
20 25.40		1.000	22.86	.900	015-91-2200		015-91-6200		015-91-3207		015-91-0200		015-91-6202		015-91-3206		015-91-3200		015-91-6203		015-91-3208		015-91-0208		015-91-5209		20	
22 27.94		1.100	25.40	1.000	015-91-2220				015-91-3227		015-91-0220				015-91-3226		015-91-3220				015-91-3228		015-91-0228		015-91-5229		22	
24 30.48		1.200	27.94	1.100	015-91-2240				015-91-3247		015-91-0240				015-91-3246		015-91-3240				015-91-3248		015-91-0248		015-91-5249		24	
26 33.02		1.300	30.48	1.200	015-91-2260		015-91-6260		015-91-3267		015-91-0260		015-91-6262		015-91-3266		015-91-3260				015-91-3268		015-91-0268		015-91-5269		26	
28 35.56		1.400	33.02	1.300	015-91-2280				015-91-3287		015-91-0280				015-91-3286		015-91-3280				015-91-3288		015-91-0288		015-91-5289		28	
30 38.10		1.500	35.56	1.400	015-91-2300				015-91-3307		015-91-0300				015-91-3306		015-91-3300				015-91-3308		015-91-0308		015-91-5309		30	
32 40.64		1.600	38.10	1.500	015-91-2320				015-91-3327		015-91-0320				015-91-3326		015-91-3320				015-91-3328		015-91-0328		015-91-5329		32	
34 43.18		1.700	40.64	1.600	015-91-2340				015-91-3347		015-91-0340				015-91-3346		015-91-3340				015-91-3348		015-91-0348		015-91-5349		34	
36 45.72		1.800	43.18	1.700	015-91-2360				015-91-3367		015-91-0360				015-91-3366		015-91-3360				015-91-3368		015-91-0368		015-91-5369		36	
38 48.26		1.900	45.72	1.800	015-91-2380				015-91-3387		015-91-0380				015-91-3386		015-91-3380				015-91-3388		015-91-0388		015-91-5389		38	
40 50.80		2.000	48.26	1.900	015-91-2400		015-91-6400		015-91-3407		015-91-0400		015-91-6402		015-91-3406		015-91-3400		015-91-6403		015-91-3408		015-91-0408		015-91-5409		40	
42 53.34		2.100	50.80	2.000	015-91-2420				015-91-3427		015-91-0420				015-91-3426		015-91-3420				015-91-3428		015-91-0428		015-91-5429		42	
44 55.88		2.200	53.34	2.100	015-91-2440				015-91-3447		015-91-0440				015-91-3446		015-91-3440				015-91-3448		015-91-0448		015-91-5449		44	
46 58.42		2.300	55.88	2.200	015-91-2460				015-91-3467		015-91-0460				015-91-3466		015-91-3460				015-91-3468		015-91-0468		015-91-5469		46	
48 60.96		2.400	58.42	2.300	015-91-2480				015-91-3487		015-91-0480				015-91-3486		015-91-3480				015-91-3488		015-91-0488		015-91-5489		48	
50 63.50		2.500	60.96	2.400	015-91-2500		015-91-6500		015-91-3507		015-91-0500		015-91-6502		015-91-3506		015-91-3500		015-91-6503		015-91-3508		015-91-0508		015-91-5509		50	
52 66.04		2.600	63.50	2.500	015-91-2520				015-91-3527		015-91-0520				015-91-3526		015-91-3520				015-91-3528		015-91-0528		015-91-5529		52	
54 68.58		2.700	66.04	2.600	015-91-2540				015-91-3547		015-91-0540				015-91-3546		015-91-3540				015-91-3548		015-91-0548		015-91-5549		54	
56 71.12		2.800	68.58	2.700	015-91-2560				015-91-3567		015-91-0560				015-91-3566		015-91-3560				015-91-3568		015-91-0568		015-91-5569		56	
58 73.66		2.900	71.12	2.800	015-91-2580				015-91-3587		015-91-0580				015-91-3586		015-91-3580				015-91-3588		015-91-0588		015-91-5589		58	
60 76.20		3.000	73.66	2.900	015-91-2600				015-91-3607		015-91-0600				015-91-3606		015-91-3600				015-91-3608		015-91-0608		015-91-5609		60	
62 78.74		3.100	76.20	3.000	015-91-2620				015-91-3627		015-91-0620				015-91-3626		015-91-3620				015-91-3628		015-91-0628		015-91-5629		62	
64 81.28		3.200	78.74	3.100	015-91-2640				015-91-3647		015-91-0640				015-91-3646		015-91-3640				015-91-3648		015-91-0648		015-91-5649		64	
66 83.82		3.300	81.28	3.200	015-91-2660				015-91-3667		015-91-0660				015-91-3666		015-91-3660				015-91-3668		015-91-0668		015-91-5669		66	
68 86.36		3.400	83.82	3.300	015-91-2680				015-91-3687		015-91-0680				015-91-3686		015-91-3680				015-91-3688		015-91-0688		015-91-5689		68	
70 88.90		3.500	86.36	3.400	015-91-2700				015-91-3707		015-91-0700				015-91-3706		015-91-3700				015-91-3708		015-91-0708		015-91-5709		70	
72 91.44		3.600	88.90	3.500	015-91-2720				015-91-3727		015-91-0720				015-91-3726		015-91-3720				015-91-3728		015-91-0728		015-91-5729		72	
74 93.98		3.700	91.44	3.600	015-91-2740				015-91-3747		015-91-0740				015-91-3746		015-91-3740				015-91-3748		015-91-0748		015-91-5749		74	
76 96.52		3.800	93.98	3.700	015-91-2760				015-91-3767		015-91-0760				015-91-3766		015-91-3760				015-91-3768		015-91-0768		015-91-5769		76	
78 99.06		3.900	96.52	3.800	015-91-2780				015-91-3787		015-91-0780				015-91-3786		015-91-3780				015-91-3788		015-91-0788		015-91-5789		78	
80 101.60		4.000	99.06	3.900	015-91-2800				015-91-3807		015-91-0800				015-91-3806		015-91-3800				015-91-3808		015-91-0808		015-91-5809		80	
82 104.14		4.100	101.60	4.000	71308-0082				71308-0482		71308-0182				71308-0582		71308-0282				71308-0682		71308-1182		71308-1282		82	
84 106.68		4.200	104.14	4.100	71308-0084				71308-0484		71308-0184				71308-0584		71308-0284				71308-0684		71308-1184		71308-1284		84	
86 109.22		4.300	106.68	4.200	71308-0086				71308-0486		71308-0186				71308-0586		71308-0286				71308-0686		71308-1186		71308-12			

13		12		11				10		9		8		7		6		5		4		3		2		1	
J		IN TAPE AND REEL WITH SHALLOW POCKET TAPE												BULK / IN TUBES										J			
		PACKAGING SEE NOTE 4. SHT 1		4-8 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										BULK		BULK							
				10-100 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										TUBES		TUBES							
		DIM. M±0.25 MM				6.10 (.240)		6.10 (.240)										8.13 (.320)		13.59 (.535)							
		PLATING				30 GOLD		15 GOLD										150 TIN		150 TIN							
		DIM. H				2.54 (.100)		2.54 (.100)										4.57 (.180)		4.57 (.180)							
I		CKTS		DIM. A		DIM. B		EDP NUMBER		EDP NUMBER								EDP NUMBER		EDP NUMBER		CKTS					
				MM	IN	MM	IN																				
		04	5.08	.200	2.54	.100																	04				
		06	7.62	.300	5.08	.200			015-91-6068														06				
		08	10.16	.400	7.62	.300			015-91-6088														08				
		10	12.70	.500	10.16	.400			015-91-6108										713088010		71308-8210		10				
		12	15.24	.600	12.70	.500																	12				
H		14	17.78	.700	15.24	.600	015-91-6148																14				
		16	20.32	.800	17.78	.700											713088016						16				
		18	22.86	.900	20.32	.800																	18				
		20	25.40	1.000	22.86	.900																	20				
		22	27.94	1.100	25.40	1.000																	22				
		24	30.48	1.200	27.94	1.100																	24				
		26	33.02	1.300	30.48	1.200																	26				
		28	35.56	1.400	33.02	1.300																	28				
G		30	38.10	1.500	35.56	1.400																	30				
		32	40.64	1.600	38.10	1.500																	32				
		34	43.18	1.700	40.64	1.600																	34				
		36	45.72	1.800	43.18	1.700																	36				
		38	48.26	1.900	45.72	1.800																	38				
		40	50.80	2.000	48.26	1.900																	40				
		42	53.34	2.100	50.80	2.000																	42				
F		44	55.88	2.200	53.34	2.100																	44				
		46	58.42	2.300	55.88	2.200																	46				
		48	60.96	2.400	58.42	2.300																	48				
		50	63.50	2.500	60.96	2.400																	50				
		52	66.04	2.600	63.50	2.500																	52				
		54	68.58	2.700	66.04	2.600																	54				
		56	71.12	2.800	68.58	2.700																	56				
E		58	73.66	2.900	71.12	2.800																	58				
		60	76.20	3.000	73.66	2.900																	60				
		62	78.74	3.100	76.20	3.000																	62				
		64	81.28	3.200	78.74	3.100																	64				
		66	83.82	3.300	81.28	3.200																	66				
		68	86.36	3.400	83.82	3.300																	68				
		70	88.90	3.500	86.36	3.400																	70				
		72	91.44	3.600	88.90	3.500																	72				
D		74	93.98	3.700	91.44	3.600																	74				
		76	96.52	3.800	93.98	3.700																	76				
		78	99.06	3.900	96.52	3.800																	78				
		80	101.60	4.000	99.06	3.900																	80				
		82	104.14	4.100	101.60	4.000																	82				
		84	106.68	4.200	104.14	4.100																	84				
		86	109.22	4.300	106.68	4.200																	86				
		88	111.76	4.400	109.22	4.300																	88				
C		90	114.30	4.500	111.76	4.400																	90				
		92	116.84	4.600	114.30	4.500																	92				
		94	119.38	4.700	116.84	4.600																	94				
		96	121.92	4.800	119.38	4.700																	96				
		98	124.46	4.900	121.92	4.800																	98				
		100	127.00	5.000	124.46	4.900																	100				
B		NO PEG VERSION										SEE SHEET 1 EC NO: UCP2014-0809 DRAWN:KIPPER 2013/08/20 CHKD:JBELL 2013/08/20 APPR:FSMITH 2013/09/03		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE		DESIGN UNITS INCH		THIRD ANGLE PROJECTION			
																mm		INCH		DRAWN BY KMS		DATE 1999/10/15				TITLE SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100	
A		(ALSO SEE SHEET 2)										K5		REV		ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DOCUMENT NO. SD-71308-001		SHEET NO. 3 OF 6			
1b_frame_C_P_AM.T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1			

13			12		11		10		9		8		7		6		5		4		3		2		1					
			PACKAGING SEE NOTE 4 SHT 1				4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		BULK		BULK					
							10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TUBES		TUBES					
							DIM. M ±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)		8.13 (.320)		8.13 (.320)			
							PLATING				150 TIN				15 GOLD				30 GOLD				150 TIN		15 GOLD		30 GOLD			
							DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)		4.57 (.180)		4.57 (.180)			
CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS					
	MM	IN	MM	IN	MM	IN																								
04	5.08	.200	2.54	.100	----	----	015-91-1041	015-91-6044	015-91-1042	015-91-6045	015-91-1043	015-91-6046	015-91-1044	015-91-0047	015-91-1040										04					
06	7.62	.300	5.08	.200	2.54	.100	015-91-1061	015-91-6064	015-91-1062	015-91-6065	015-91-1063	015-91-6066	015-91-1064	015-91-0067	015-91-1060										06					
08	10.16	.400	7.62	.300	5.08	.200	015-91-1081	015-91-6084	015-91-1082	015-91-6085	015-91-1083	015-91-6086	015-91-1084	015-91-0087	015-91-1080										08					
10	12.70	.500	10.16	.400	7.62	.300	015-91-1101	015-91-6104	015-91-1102	015-91-6105	015-91-1103	015-91-6106	015-91-1104	015-91-0107	015-91-1100										10					
12	15.24	.600	12.70	.500	10.16	.400	015-91-1121		015-91-1122		015-91-1123		015-91-1124	015-91-0127	015-91-1120										12					
14	17.78	.700	15.24	.600	12.70	.500	015-91-1141	015-91-6144	015-91-1142	015-91-6145	015-91-1143	015-91-6146	015-91-1144	015-91-0147	015-91-1140										14					
16	20.32	.800	17.78	.700	15.24	.600	015-91-1161	015-91-6164	015-91-1162	015-91-6165	015-91-1163	015-91-6166	015-91-1164	015-91-0167	015-91-1160										16					
18	22.86	.900	20.32	.800	17.78	.700	015-91-1181		015-91-1182		015-91-1183		015-91-1184	015-91-0187	015-91-1180										18					
20	25.40	1.000	22.86	.900	20.32	.800	015-91-1201		015-91-1202		015-91-1203		015-91-1204	015-91-0207	015-91-1200										20					
22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1221		015-91-1222		015-91-1223		015-91-1224	015-91-0227	015-91-1220										22					
24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1241	71308-6901	015-91-1242		015-91-1243		015-91-1244	015-91-0247	015-91-1240										24					
26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1261		015-91-1262		015-91-1263		015-91-1264	015-91-0267	015-91-1260										26					
28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1281		015-91-1282		015-91-1283		015-91-1284	015-91-0287	015-91-1280										28					
30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1301		015-91-1302		015-91-1303		015-91-1304	015-91-0307	015-91-1300										30					
32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1321		015-91-1322		015-91-1323		015-91-1324	015-91-0327	015-91-1320										32					
34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1341		015-91-1342		015-91-1343		015-91-1344	015-91-0347	015-91-1340										34					
36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1361		015-91-1362		015-91-1363		015-91-1364	015-91-0367	015-91-1360										36					
38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1381		015-91-1382		015-91-1383		015-91-1384	015-91-0387	015-91-1380										38					
40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1401		015-91-1402		015-91-1403		015-91-1404	015-91-0407	015-91-1400										40					
42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1421		015-91-1422		015-91-1423		015-91-1424	015-91-0427	015-91-1420										42					
44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1441		015-91-1442		015-91-1443		015-91-1444	015-91-0447	015-91-1440										44					
46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1461		015-91-1462		015-91-1463		015-91-1464	015-91-0467	015-91-1460										46					
48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1481		015-91-1482		015-91-1483		015-91-1484	015-91-0487	015-91-1480										48					
50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1501	015-91-6504	015-91-1502	015-91-6505	015-91-1503	015-91-6506	015-91-1504	015-91-0507	015-91-1500										50					
52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1521		015-91-1522		015-91-1523	71308-5203	015-91-1524	015-91-0527	015-91-1520										52					
54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1541		015-91-1542		015-91-1543		015-91-1544	015-91-0547	015-91-1540										54					
56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1561		015-91-1562		015-91-1563		015-91-1564	015-91-0567	015-91-1560										56					
58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1581		015-91-1582		015-91-1583		015-91-1584	015-91-0587	015-91-1580										58					
60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1601		015-91-1602		015-91-1603		015-91-1604	015-91-0607	015-91-1600										60					
62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1621		015-91-1622		015-91-1623		015-91-1624	015-91-0627	015-91-1620										62					
64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1641		015-91-1642		015-91-1643		015-91-1644	015-91-0647	015-91-1640										64					
66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1661		015-91-1662		015-91-1663		015-91-1664	015-91-0667	015-91-1660										66					
68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1681		015-91-1682		015-91-1683		015-91-1684	015-91-0687	015-91-1680										68					
70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1701		015-91-1702		015-91-1703		015-91-1704	015-91-0707	015-91-1700										70					
72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1721		015-91-1722		015-91-1723		015-91-1724	015-91-0727	015-91-1720										72					
74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1741		015-91-1742		015-91-1743		015-91-1744	015-91-0747	015-91-1740										74					
76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1761		015-91-1762		015-91-1763		015-91-1764	015-91-0767	015-91-1760										76					
78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1781		015-91-1782		015-91-1783		015-91-1784	015-91-0787	015-91-1780										78					
80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1801		015-91-1802		015-91-1803		015-91-1804	015-91-0807	015-91-1800										80					
82	104.14	4.100	101.60	4.000	99.06	3.900	71308-4082		71308-4182		71308-4282		71308-5082	71308-5182	71308-5282										82					
84	106.68	4.200	104.14	4.100	101.60	4.000	71308-4084		71308-4184		71308-4284		71308-5084	71308-5184	71308-5284										84					
86	109.22	4.300	106.68	4.200	104.14	4.100	71308-4086		71308-4186		71308-4286		71308-5086	71308-5186	71308-5286										86					
88	111.76	4.400	109.22	4.300	106.68	4.200	71308-4088		71308-4188		71308-4288		71308-5088	71308-5188	71308-5288										88					
90	114.30	4.500	111.76	4.400	109.22	4.300	71308-4090		71308-4190		71308-4290		71308-5090	71308-5190	71308-5290															

[illegible]

		13		12		11		10		9		8		7		6		5		4		3		2		1									
J		PEG OPTION																										J							
		NO PEG VERSION												NO PEG VERSION				LONG PEG VERSION (.130")				SHORT PEG VERSION (.055")													
		PACKAGING SEE NOTE 4, SHT 1		4-6 CKT		BULK	TAPE-N-REEL W/VAC CAPS		N/A		4-8 CKT		TAPE-N-REEL W/VAC CAPS		BULK		BULK		BULK		TAPE-N-REEL W/VAC CAPS		BULK		BULK		TAPE-N-REEL W/ VAC CAPS								
				8-100 CKT		TUBES		TAPE-N-REEL W/VAC CAPS		TUBES W/ VAC CAPS			10-100 CKT		TAPE-N-REEL W/VAC CAPS		TUBES		TUBES		TUBES		TAPE-N-REEL W/VAC CAPS		TUBES		BULK		TAPE-N-REEL W/ VAC CAPS						
		DIM. M±0.25 MM				6.10 (.240)				8.13(.320)				13.59(.535)				6.10(.240)				8.13(.320)				6.10 (.240)									
PLATING				59 TIN				59 TIN				59 TIN				59 TIN				59 TIN															
I		DIM. H				2.54(.100)				4.57(.180)				4.57(.180)				2.54(.100)				4.57(.180)				2.54(.100)									
		CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS									
			MM	IN	MM	IN	MM	IN																											
			04	5.08	.200	2.54	.100	---																			---	71308-5404	71308-5504	N/A	71308-6404	71308-6504	71308-6604	71308-6706	71308-6806
			06	7.62	.300	5.08	.200	2.54																			.100	71308-5406	71308-5506	N/A	71308-6406	71308-6506	71308-6606	71308-6706	71308-6806
H		08	10.16	.400	7.62	.300	5.08	.200	71308-5408	71308-5508	71308-5608	71308-6408	71308-6508	71308-6608	71308-6708	71308-6808																			
		10	12.70	.500	10.16	.400	7.62	.300	71308-5410	71308-5510	71308-5610	71308-6410	71308-6510	71308-6610	71308-6710	71308-6810																			
		12	15.24	.600	12.70	.500	10.16	.400	71308-5412	71308-5512	71308-5612	71308-6412	71308-6514	71308-6612																					
		14	17.78	.700	15.24	.600	12.70	.500	71308-5414	71308-5514	71308-5614	71308-6414	71308-6514	71308-6614																					
		16	20.32	.800	17.78	.700	15.24	.600	71308-5416	71308-5516	71308-5616	71308-6416	71308-6516	71308-6616																					
G		18	22.86	.900	20.32	.800	17.78	.700	71308-5418		71308-5618	71308-6418		71308-6618																					
		20	25.40	1.000	22.86	.900	20.32	.800	71308-5420	71308-5520	71308-5620	71308-6420		71308-6620																					
		22	27.94	1.100	25.40	1.000	22.86	.900	71308-5422		71308-5622	71308-6422		71308-6622																					
		24	30.48	1.200	27.94	1.100	25.40	1.000	71308-5424		71308-5624	71308-6424		71308-6624																					
		26	33.02	1.300	30.48	1.200	27.94	1.100	71308-5426		71308-5626	71308-6426		71308-6626	71308-6726																				
F		28	35.56	1.400	33.02	1.300	30.48	1.200	71308-5428		71308-5628	71308-6428		71308-6628																					
		30	38.10	1.500	35.56	1.400	33.02	1.300	71308-5430		71308-5630	71308-6430		71308-6630																					
		32	40.64	1.600	38.10	1.500	35.56	1.400	71308-5432		71308-5632	71308-6432		71308-6632																					
		34	43.18	1.700	40.64	1.600	38.10	1.500	71308-5434		71308-5634	71308-6434		71308-6634																					
		36	45.72	1.800	43.18	1.700	40.64	1.600	71308-5436		71308-5636	71308-6436		71308-6636																					
E		38	48.26	1.900	45.72	1.800	43.18	1.700	71308-5438		71308-5638	71308-6438		71308-6638																					
		40	50.80	2.000	48.26	1.900	45.72	1.800	71308-5440	71308-5540	71308-5640	71308-6440		71308-6640																					
		42	53.34	2.100	50.80	2.000	48.26	1.900	71308-5442		71308-5642	71308-6442		71308-6642																					
		44	55.88	2.200	53.34	2.100	50.80	2.000	71308-5444		71308-5644	71308-6444		71308-6644																					
		46	58.42	2.300	55.88	2.200	53.34	2.100	71308-5446		71308-5646	71308-6446		71308-6646																					
D		48	60.96	2.400	58.42	2.300	55.88	2.200	71308-5448		71308-5648	71308-6448		71308-6648																					
		50	63.50	2.500	60.96	2.400	58.42	2.300	71308-5450	71308-5550	71308-5650	71308-6450	71308-6550	71308-6650																					
		52	66.04	2.600	63.50	2.500	60.96	2.400	71308-5452		71308-5652	71308-6452		71308-6652																					
		54	68.58	2.700	66.04	2.600	63.50	2.500	71308-5454		71308-5654	71308-6454		71308-6654																					
		56	71.12	2.800	68.58	2.700	66.04	2.600	71308-5456		71308-5656	71308-6456		71308-6656																					
C		58	73.66	2.900	71.12	2.800	68.58	2.700	71308-5458		71308-5658	71308-6458		71308-6658																					
		60	76.20	3.000	73.66	2.900	71.12	2.800	71308-5460		71308-5660	71308-6460		71308-6660																					
		62	78.74	3.100	76.20	3.000	73.66	2.900	71308-5462		71308-5662	71308-6462		71308-6662																					
		64	81.28	3.200	78.74	3.100	76.20	3.000	71308-5464		71308-5664	71308-6464		71308-6664																					
		66	83.82	3.300	81.28	3.200	78.74	3.100	71308-5466		71308-5666	71308-6466		71308-6666																					
B		68	86.36	3.400	83.82	3.300	81.28	3.200	71308-5468		71308-5668	71308-6468		71308-6668																					
		70	88.90	3.500	86.36	3.400	83.82	3.300	71308-5470		71308-5670	71308-6470		71308-6670																					
		72	91.44	3.600	88.90	3.500	86.36	3.400	71308-5472		71308-5672	71308-6472		71308-6672																					
		74	93.98	3.700	91.44	3.600	88.90	3.500	71308-5474		71308-5674	71308-6474		71308-6674																					
		76	96.52	3.800	93.98	3.700	91.44	3.600	71308-5476		71308-5676	71308-6476		71308-6676																					
A		78	99.06	3.900	96.52	3.800	93.98	3.700	71308-5478		71308-5678	71308-6478		71308-6678																					
		80	101.60	4.000	99.06	3.900	96.52	3.800	71308-5480		71308-5680	71308-6480		71308-6680																					
		82	104.14	4.100	101.60	4.000	99.06	3.900	71308-5482		71308-5682	71308-6482		71308-6682																					
		84	106.68	4.200	104.14	4.100	101.60	4.000	71308-5484		71308-5684	71308-6484		71308-6684																					
		86	109.22	4.300	106.68	4.200	104.14	4.100	71308-5486		71308-5686	71308-6486		71308-6686																					
A		88	111.76	4.400	109.22	4.300	106.68	4.200	71308-5488		71308-5688	71308-6488		71308-6688																					
		90	114.30	4.500	111.76	4.400	109.22	4.300	71308-5490		71308-5690	71308-6490		71308-6690																					
		92	116.84	4.600	114.30	4.500	111.76	4.400	71308-5492		71308-5692	71308-6492		71308-6692																					
		94	119.38	4.700	116.84	4.600	114.30	4.500	71308-5494		71308-5694	71308-6494		71308-6694																					
		96	121.92	4.800	119.38	4.700	116.84	4.600	71308-5496		71308-5696	71308-6496		71308-6696																					
A		98	124.46	4.900	121.92	4.800	119.38	4.700	71308-5498		71308-5698	71308-6498		71308-6698																					
		100	127.00	5.000	124.46	4.900	121.92	4.800	71308-5500		71308-5700	71308-6500		71308-6700																					
		59 TIN PLATE ASSEMBLIES																																	
		REV	K5	DESCRIPTION 2013/08/20 2013/08/20 2013/08/20 2013/09/03 DRWN:KJPPER CHKD:JBELL APPR:FSMITH	QUALITY SYMBOLS ☒=0 ☒=0 ☒=0	GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE MM/IN				SCALE		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		TITLE SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100 molex	DOCUMENT NO. SD-71308-001	SHEET NO. 6 OF 6													
						mm		INCH		DRAWN BY KMS		DATE 1999/10/15		CHECKED BY KMS		DATE 1999/10/15		APPROVED BY KMS					DATE 1999/10/15												
ANGULAR ±1/2°						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						MATERIAL NO. SEE TABLE																							
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																			
1b_frame_C_P_AM.T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1											