

CONFIGURATION	PART NUMBER	LENGTH
Cable Assembly, Molded, 14Awg, Standard Flex, Connectors - Male Straight Entry/ Female Straight Entry	P29008-MXX	AS REQUESTED
DIMENSIONS		
(mm)		
		
		
TECHNICAL DATA		
TEMPERATURE RANGE:	-20C to +90C	
PROTECTION:	IP 67, NEMA 6P	
BODY:	OIL RESISTANT PVC	
CONTACTS:	COPPER ALLOY	
CONTACT PLATING:	GOLD OVER NICKEL PLATING	
CONNECTOR FACE:	PVC BLACK	
AMPERAGE:	15AMP	
COUPLER:	MACHINED ALUMINUM, ANODIZED	
CABLE CHARACTERISTICS:	UL TYPE TC 600V 90°C DRY 75°C WET, EXPOSED RUN (ER) OR MTW 600V 90°C OR STOOW 105°C 600V - CSA STOOW 600V FT2	
APPROVALS:	UL, c(UL)	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[P29008-M1](#) [P29008-M2](#) [P29008-M3](#) [P29008-M4](#) [P29008-M5](#) [P29008-M6](#) [P29008-M8](#) [P29008-M10](#) [P29008-M0.5](#)
[P29008-M1.5](#) [P29008-M2.5](#) [P29008-M12](#) [P29008-M14](#)