


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	8						
			AC2	REVISED PER ECO-11-004917	11MAR11	RK	HMR

D


C

B

A





MARKING
SEE TABLE



MATING FACE


Y ±0.25
[±.010]



RECOMMENDED PANEL CUTOUT

- 1. PHENOLIC PER MIL-M-14, TYPE CFG, BLACK.
- 2. DIALLYL PHTHALATE PER MIL-M-14, TYPE SDG-F, BLUE.
- 3. AMP PART NO THIS AREA. DATE CODE AT AMP'S OPTION.
- 4. MARK KS 21303, L10.
- 5. WHEN MATING WITH BLOCK 201357, ACCOMODATES TYPE II, TYPE III+ OR TYPE VI #16 PIN OR SOCKET CONTACTS.
- 6. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	43.08 [1.696]	3.86 [.152]	3 4	2	200838-9
	43.08 [1.696]	3.86 [.152]	3	2	200838-3
	42.82 [1.686]	3.99 [.157]	3	1	200838-2
	Z	Y	MARKING	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.REIFSNYDER 07 DEC 95	 TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK R.STONE 29 FEB 96					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± ± 0.13 [.005] 3 PLC ± ± - 4 PLC ± ± - ANGLES ± ± 1°	APVD G.A.STEINHAUER 20 MAR 96	NAME BLOCK, FEMALE, 34 PLACE MINIATURE RECTANGULAR, M SERIES				
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		WEIGHT —					
MATERIAL SEE TABLE	FINISH —	CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C-200838	RESTRICTED TO —
				SCALE 3:1	SHEET 1 of 1	REV AC2	