

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300410012](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Mini-Change A-Size Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 18 AWG, PVC Cable, 10.0m (32.81') Length, Nickel (Ni) Plated Brass Coupler

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Industrial Cordsets
Series [130041](#)
Connector End A Mini-Change
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Mini-Change Connectors](#)
Product Name Mini-Change
Protocol N/A
Region America, Asia, Europe
Type Single Ended
UPC 78172504924

Physical
Cable Diameter 7.37mm (.290")
Cable Length 10.0m (32.81')
Color - Cable Jacket Orange
Coupling Style Threaded
Gender Female-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Coupling Nut Nickel-plated Brass
Material - Plating Mating Gold
Orientation Straight to Pigtail
Poles 4
Temperature Range - Operating -40°C to +105°C
Wire Size AWG 18
Wire/Cable Type N/A

Electrical
Current - Maximum per Contact 7.0A
Voltage - Maximum 300V

Material Info
Engineering Number 104000D09M100

Reference - Drawing Numbers
Sales Drawing SD-130041-001



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130041](#) Series