



# TLS 2200®/TLS PC Link™ Labels

## TLS 2200®/TLS PC Link™ Label Index By Size (Continued)

| Diagram       | Catalog Number    | Labels Per Roll | Material      | Color           | B-Number | Label Width<br>Inch (mm) A | Label Height<br>Inch (mm) B | Write-On Height<br>Inch (mm) C | Wire<br>Gauge |
|---------------|-------------------|-----------------|---------------|-----------------|----------|----------------------------|-----------------------------|--------------------------------|---------------|
| <b>1.625"</b> |                   |                 |               |                 |          |                            |                             |                                |               |
| Fig. 4        | PTL-76-490        | 250             | Polyester     | White           | B-490    | 1.625 (41.3)               | 0.600 (15.2)                | —                              | —             |
| Fig. 4        | PTL-76-490        | 250             | Polyester     | White           | B-490    | 1.625 (41.3)               | 0.600 (15.2)                | —                              | —             |
| <b>1.630"</b> |                   |                 |               |                 |          |                            |                             |                                |               |
| Fig. 30       | PTL-35-422-PROP   | 250             | Polyester     | Gray            | B-422    | 1.630 (41.4)               | 0.750 (19.1)                | —                              | —             |
| Fig. 30       | PTL-35-423-PROP   | 250             | Polyester     | Gray            | B-423    | 1.630 (41.4)               | 0.750 (19.1)                | —                              | —             |
| Fig. 30       | PTL-35-428-PROP   | 250             | Polyester     | Gray            | B-428    | 1.630 (41.4)               | 0.750 (19.1)                | —                              | —             |
| Fig. 30       | PTL-35-435-PROP   | 250             | Polyester     | Gray            | B-435    | 1.630 (41.4)               | 0.750 (19.1)                | —                              | —             |
| Fig. 30       | PTL-35-423-PROP   | 250             | Polyester     | Black on Silver | B-423    | 1.630 (41.4)               | 0.750 (19.1)                | —                              | —             |
| Fig. 30       | PTL-35-435-PROP   | 250             | Polyester     | Black on Silver | B-435    | 1.630 (41.4)               | 0.750 (19.1)                | —                              | —             |
| <b>1.750"</b> |                   |                 |               |                 |          |                            |                             |                                |               |
| Fig. 7        | PTL-87-427        | 250             | Vinyl         | White           | B-427    | 1.750 (44.5)               | 1.000 (25.4)                | 0.375 (9.5)                    | 12 to 10      |
| Fig. 26       | PTL-110-145-GY    | 100             | Polyethylene  | Gray            | B-145    | 1.750 (44.5)               | 1.000 (25.4)                | —                              | —             |
| Fig. 26       | BPTL-110-145-GY   | 1000            | Polyethylene  | Gray            | B-145    | 1.750 (44.5)               | 1.000 (25.4)                | —                              | —             |
| Fig. 26       | BPTL-110-145FR-GY | 1,000           | Polyethylene  | Gray            | B-145    | 1.750 (44.5)               | 1.000 (25.4)                | —                              | —             |
| Fig. 26       | PTL-110-145FR-GY  | 100             | Polyethylene  | Gray            | B-145    | 1.750 (44.5)               | 1.000 (25.4)                | —                              | —             |
| Fig. 23       | PTLFP-02-425      | 100             | Polypropylene | White           | B-425    | 1.750 (44.5)               | 1.000 (25.4)                | —                              | —             |
| Fig. 7        | PTL-88-427        | 250             | Vinyl         | White           | B-427    | 1.750 (44.5)               | 1.500 (38.1)                | 0.500 (12.7)                   | 10 to 4       |
| Fig. 6        | PTL-160-499       | 100             | Nylon         | White           | B-499    | 1.750 (44.5)               | 1.875 (47.6)                | —                              | —             |
| <b>1.765"</b> |                   |                 |               |                 |          |                            |                             |                                |               |
| Fig. 20       | PSPT-094-175-WT   | 100             | Polyolefin    | White           | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | 28 to 18      |
| Fig. 20       | BPSPT-094-175-WT  | 2500            | Polyolefin    | White           | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | 28 to 18      |
| Fig. 20       | PSPT-094-175-YL   | 100             | Polyolefin    | Yellow          | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | 28 to 18      |
| Fig. 20       | BPSPT-094-175-WT  | 2,500           | Polyolefin    | White           | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-BK   | 100             | Polyolefin    | Black           | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-BL   | 100             | Polyolefin    | Blue            | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-BR   | 100             | Polyolefin    | Brown           | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-GR   | 100             | Polyolefin    | Green           | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-GY   | 100             | Polyolefin    | Grey            | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-OR   | 100             | Polyolefin    | Orange          | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-PK   | 100             | Polyolefin    | Pink            | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-RD   | 100             | Polyolefin    | Red             | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-VT   | 100             | Polyolefin    | Violet          | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-WT   | 100             | Polyolefin    | White           | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-094-175-YL   | 100             | Polyolefin    | Yellow          | B-342    | 1.765 (44.8)               | 0.182 (4.6)                 | —                              | —             |
| Fig. 20       | PSPT-125-175-WT   | 100             | Polyolefin    | White           | B-342    | 1.765 (44.8)               | 0.235 (6.0)                 | —                              | 22 to 16      |
| Fig. 20       | BPSPT-125-175-WT  | 1000            | Polyolefin    | White           | B-342    | 1.765 (44.8)               | 0.235 (6.0)                 | —                              | 22 to 16      |

