


Series KRPA General Purpose Relays



- Multi-Contact Arrangement
► Octal Plug Termination
► Clear Dust Cover
- Hold-Down Spring for KRPA and KRPA-N Will Accommodate Machine Screws or Rivets; for Use with Flush Mount Chassis Sockets


U.L. Contact Ratings for KRPA			
Material	Silver	Silver-Cadmium Oxide	
Code	Y	G	
Models	SPDT, DPDT and 3PDT	SPDT, DPDT	3PDT
Ratings	5 amps @ 120 VAC 1/10 HP @ 120 VAC 3 amps @ 240 VAC 1/6 HP @ 240 VAC	10 amps @ 250 VAC 1/3 HP @ 250 VAC 1/6 HP @ 120 VAC	10 amps @ 120 VAC 1/6 HP @ 120 VAC 6 amps @ 250 VAC 1/3 HP @ 250 VAC

Ruggedly constructed relay offered with silver contacts, code “Y”, rated 5 amps; and silver-cadmium oxide contacts, code “G” rated 10 amps. Contact arrangements are available up through 3 form (3PDT). Expected life exceeds 100,000 operations at rated load. Mechanical life is 10 million operations, minimum. Enclosed in a clear dust cover. U.L. recognized under file E22575. Low cost version of the KRP relay.

KRPA-N Series has an indicator lamp wired in parallel with its coil, making this model ideal for voltage or current monitoring applications. Silver-cadmium oxide contacts are rated 10 amps. KRPA-N specifications are identical to those of other models in the KRPA series.

Stock No.	Mfr.'s Type	EACH		
		1-24	25-49	50-99
886-0606	KRPA-5AG-120	20.27	18.40	16.71
886-0615	KRPA-11AY-6	17.77	16.90	15.99
886-0616	KRPA-11AY-12	22.15	20.13	18.27
886-0617	KRPA-11AY-24	21.11	20.07	18.80
886-0618	KRPA-11AY-120	19.19	17.46	15.85
886-0620	KRPA-11AG-6	22.67	20.60	18.70
886-0621	KRPA-11AG-12	22.67	20.60	18.70
886-0622	KRPA-11AG-24	19.08	17.34	15.74
886-0623	KRPA-11AG-120	16.99	15.46	14.03
886-0626	KRPA-11DY-12	19.84	18.87	17.87
886-0627	KRPA-11DY-24	19.86	18.88	17.86
886-0631	KRPA-11DG-12	19.64	17.85	16.20
886-0632	KRPA-11DG-24	19.64	17.84	16.21
886-0634	KRPA-11DG-110	21.10	19.18	17.58
886-0637	KRPA-14AY-24	19.65	17.87	16.22
886-0638	KRPA-14AY-120	27.11	24.65	22.38
886-0641	KRPA-14AG-12	21.75	20.66	19.58
886-0642	KRPA-14AG-24	27.89	25.35	23.02
886-0643	KRPA-14AG-120	24.17	21.97	19.94
886-0647	KRPA-14DY-24	21.10	20.07	19.02
886-0651	KRPA-14DG-12	27.69	25.17	22.85
886-0652	KRPA-14DG-24	27.41	24.92	22.86
886-0654	KRPA-14DG-110	24.08	22.86	21.67
886-0656	KRPA-11AN-12	20.17	19.16	18.15
886-0657	KRPA-11AN-24	24.26	23.04	21.83
886-0658	KRPA-11AN-120	22.13	20.11	18.45
886-0661	KRPA-11DN-12	24.33	23.11	21.69
886-0662	KRPA-11DN-24	22.01	20.01	18.35
886-0663	KRPA-11DN-110	22.25	21.14	20.03
886-0667	KRPA-14AN-120	26.98	24.53	22.48

T9A Series



T9A Series are low cost, printed circuit board or panel mount relays. Up to 30 A switching in SPST and 20 A in SPDT arrangements. Silver-cadmium oxide contacts in 1 Form A (SPST-NO) and 1 Form C (SPDT). Available in unsealed, plastic dust cover (T9AP) or immersion cleanable, sealed plastic case (T9AS). UL Class F insulation system standard. Well suited for various industrial, commercial and residential applications.

Stock No.	Mfr.'s Type	Volts (DC)	Termination	Contacts	EACH		
					1-24	25-49	50-Up
886-2101	T9AS1D12-12	12	P.C. Mount	SPST-NO	3.10	2.74	2.48
886-2102	T9AS5D12-12	12	P.C. Mount	SPDT	2.66	2.29	2.09
886-2103	T9AS1D12-24	24	P.C. Mount	SPST-NO	3.10	2.74	2.48
886-2104	T9AS5D12-24	24	P.C. Mount	SPDT	2.70	2.38	2.19
886-2106	T9AS1D12-18	18	P.C. Mount	SPST-NO	2.70	2.38	2.19
886-2107	T9AP5D52-12	12	Flange Mount, Q.C.	SPDT	3.82	3.37	3.06
886-2108	T9AP5D52-24	24	Flange Mount, Q.C.	SPDT	3.81	3.38	3.06
886-2109	T9AS1D22-12	12	P.C. Mount, Q.C.	SPST-NO	3.35	2.97	2.69
886-2110	T9AS1D22-24	24	P.C. Mount, Q.C.	SPST-NO	2.95	2.66	2.43
886-2111	T9AS5D22-12	12	P.C. Mount, Q.C.	SPDT	2.95	2.66	2.43
886-2112	T9AS5D22-24	24	P.C. Mount, Q.C.	SPDT	2.95	2.61	2.36