


RoHS



GSGX Series Right Angle Gang Jack

Features   

- Available in up to 8 Ports
- Available Fully Shielded for Category 5 Applications
- Standard and Reflow Compatible Through Hole Designs Available
- CSA/NRTL Certified File No. LR78160

Performance Specifications

Materials and Finish

Housing Material

PBT Thermoplastic, Glass Filled, UL94V-0 Rated, Black Color

Shield

Copper Alloy, Nickel Plated

Contact Material

Phosphor Bronze

Electrical Characteristics

Insulation Resistance

500 Megohms Min

Dielectric Withstanding Voltage

1000V AC for 1 Minute

Contact Resistance

20 Milliohms Max

Current Rating

1.5 Amps

MODULAR JACKS AND PLUGS

GSGX Series

Documentation & Ordering Information

Kycon Part #

Part Number Builder

Series	Shield Option	No. of Ports	No. of Positions	No. of Contacts	Ground Pin Spacing	Plating Option
--------	---------------	--------------	------------------	-----------------	--------------------	----------------

Series

GSGX - Right Angle Gang Jack P.C.B. Mount

Ground Pin Spacing

Blank - No ground pin spacing

3.68mm - 3.68mm ground pin spacing

4.57mm - 4.57mm ground pin spacing

No. of Port and Shield Options

No. of Port	N Non-Shielded			NS Shielded			NS2 Shielded w/Top Only ground Tabs			NS7 Shielded w/Top & Side ground Tabs			NSX		
	Blank	3.68 mm	4.57 mm	Blank	3.68 mm	4.57 mm	Blank	3.68 mm	4.57 mm	Blank	3.68 mm	4.57 mm	Blank	3.68 mm	4.57 mm
2	-	-	-	-	-	-	-	-	-	-	-	*	-	-	-
4	-	-	-	-	-	-	-	-	-	-	*	-	-	-	**
5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
6	-	-	-	-	-	-	-	-	-	-	-	-	**	-	-
8	-	-	-	-	*	-	-	-	-	-	-	-	-	-	-
10	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
12	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

* Not available with 50μ" Gold Plating

** Available only as 50μ" Gold Plating

Plating Option

Blank - Standard

50 - 50μ" Gold Plating

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[GSGX-NS7-888-45750](#) [GSGX-NS7-888-457](#)