

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130102-0260](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Safeway® Phenolic Hand Lamp with 100W Screw Release Guard with Reflector with Switch and Side Outlet, Cord Type 16/3 SJTOW, Cord Length 7.62m (25.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130102](#)
NEMA Configuration NEMA 5-15
Outlet Side
Overview [Hand Lamps](#)
Product Literature Order No 987650-8053
Product Name Safety Yellow®
Type Hand Lamps
UPC 78678879532
Woodhead Yes

Physical

Cord Length - Primary 7.62m (25.0')
Cord Length - Secondary N/A
Depth 101.60mm (4.000")
Duty Commercial
Guard Included No
Guard Type Metal Wire
Height 381.00mm (15.000")
Length N/A
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SJTOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch Yes
Voltage (Fixture) - Maximum 240V

Material Info

Old Part Number 271USA163



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[130102Series](#)