

Miniature Steel Alligator Clip, 5 Amp

Features

- Nickel Plated
- Crimp or Solder Connection
- Overall Length: 1.100" (27.9mm)
- Jaw Opening: .190" (4.8mm)

NTE Type No.	Description
72-123	Miniature Steel Alligator Clip

See page 24 for recommended insulators.



See page 15 for clip & insulator combinations.

Miniature Solid Copper Alligator Clip, 5 Amp

Features

- Crimp or Solder Connection
- Overall Length: 1.100" (27.9mm)
- Jaw Opening: .190" (4.8mm)

NTE Type No.	Description
72-125	Miniature Solid Copper Alligator Clip

See page 24 for recommended insulators.



See page 15 for clip & insulator combinations.


Mini Steel Alligator Clip w/Barrel, 5 Amp

Features

- Nickel Plated
- Crimp or Solder Connection Barrel Tail
- Overall Length: 1.250" (31.7mm)
- Jaw Opening: .190" (4.8mm)

NTE Type No.	Description
72-124	Miniature Steel Alligator Clip with Barrel

See page 24 for recommended insulators.



See page 15 for clip & insulator combinations.

Mini Steel Alligator Clip w/Threaded Barrel, 5 Amp

Features

- Nickel Plated
- 6-32 UNC Threaded Barrel Connection
- Overall Length: 1.500" (38.1mm)
- Jaw Opening: .190" (4.8mm)

NTE Type No.	Description
72-126	Miniature Steel Alligator Clip with Threaded Barrel

See page 24 for recommended insulators.



Steel Alligator Clip, 5 Amp

Features

- Nickel Plated Clip
- Crimp/Solder Connection
- Overall Length: 1.690" (42.9mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-159	Steel Alligator Clip

See page 26 for recommended insulators.



See page 16 for clip & insulator combinations.

Steel Alligator Clip w/Screw, 5 Amp

Features

- Nickel Plated Clip
- 6-40 Screw or Crimp Connection
- Overall Length: 1.690" (42.86mm)
- Jaw Opening: .310" (7.9mm)

NTE Type No.	Description
72-186	Steel Alligator Clip with Screw



Toothless Steel Alligator Clip, 5 Amp

Features

- Smooth Micro Tipped Jaws
- Crimp or Solder Connection
- Overall Length: 1.100" (27.9mm)
- Jaw Opening: .220" (5.58mm)

NTE Type No.	Description
72-129	Toothless Steel Alligator Clip

See page 24 for recommended insulators.



See page 15 for clip & insulator combinations.

Toothless Solid Copper Alligator Clip, 5 Amp

Features

- Smooth Micro Tipped Jaws
- Crimp or Solder Connection
- Overall Length: 1.100" (27.9mm)
- Jaw Opening: .220" (5.58mm)

NTE Type No.	Description
72-130	Toothless Solid Copper Alligator Clip

See page 24 for recommended insulators.



See page 16 for clip & insulator combinations.

Steel Alligator Clip w/Barrel, 10 Amp

Features

- Nickel Plated
- Crimp/Solder or Banana Plug Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-148	Steel Alligator Clip with Barrel

See page 25 for recommended insulators.



See page 16 for clip & insulator combinations.

Solid Copper Alligator Clip w/Barrel, 10 Amp

Features

- Crimp/Solder or Banana Plug Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-149	Solid Copper Alligator Clip with Barrel

See page 25 for recommended insulators.



See page 17 for clip & insulator combinations.

Solid Copper Alligator Clip w/Barrel & Screw, 10 Amp

Features

- Screw Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-151	Solid Copper Alligator Clip with Barrel & Screw

See page 25 for recommended insulators.



See page 17 for clip & insulator combinations.

Steel Alligator Clip w/Barrel & Screw, 10 Amp

Features

- Nickel Plated
- Screw Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-153	Steel Alligator Clip with Barrel & Screw

See page 25 for recommended insulators.



See page 17 for clip & insulator combinations.

Steel Alligator Clip w/Threaded Barrel, 10 Amp

Features

- Nickel Plated
- 8-32 UNC Threaded Barrel Connection
- Overall Length: 2.125" (53.9mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-154	Steel Alligator Clip with Threaded Barrel

See page 25 for recommended insulators.



See page 17 for clip & insulator combinations.

Steel Alligator Clip w/U-Shaped Tail, 10 Amp

Features

- Nickel Plated Clip
- Crimp/Solder Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-155	Steel Alligator Clip with U-Shaped Tail

See page 25 for recommended insulators.



See page 18 for clip & insulator combinations.

Stainless Steel Alligator Clip w/Barrel, 10 Amp

Features

- Crimp/Solder or Banana Plug Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-156	Stainless Steel Alligator Clip with Barrel

See page 25 for recommended insulators.



See page 18 for clip & insulator combinations.

Solid Copper Alligator Clip, 10 Amp

Features

- Crimp/Solder Connection
- Overall Length: 1.690" (42.9mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-160	Solid Copper Alligator Clip

See page 26 for recommended insulators.



See page 18 for clip & insulator combinations.

Phone Tip Steel Alligator Clip, 10 Amp

Features

- Nickel Plated Clip
- Accepts Standard Phone Tip or Test Probe Tip
- Overall Length: 1.970" (50mm)
- Jaw Opening: .310" (7.9mm)

NTE Type No.	Description
72-181	Phone Tip Steel Alligator Clip

See page 25 for recommended insulators.



Solid Copper Alligator Clip w/Screw, 10 Amp

Features

- 6-40 Screw or Crimp Connection
- Overall Length: 1.690" (42.86mm)
- Jaw Opening: .310" (7.9mm)

NTE Type No.	Description
72-187	Solid Copper Alligator Clip with Screw



Steel Alligator Clip, Fang Tooth w/Barrel

Features

- Nickel Plated Clip
- Crimp/Solder or Banana Plug Connection
- Grips Both Fine and Thick Conductors
- Overall Length: 1.920" (48.7mm)
- Jaw Opening: .390" (9.9mm)

NTE Type No.	Description
72-098	Steel Alligator Clip, Fang Tooth with Barrel




Steel Alligator Clip w/Barrel, Screw & Handle, 10 Amp

Features

- Nickel Plated Clip with Insulated Handle
- Banana Plug or Screw Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-152-0	Steel Alligator Clip with Barrel, Screw and Black Insulated Handle
72-152-2	Steel Alligator Clip with Barrel, Screw and Red Insulated Handle
72-152-KIT	2 Each of 72-152-0 (Black) & 72-152-2 (Red)



Solid Copper Alligator Clip w/Barrel, Screw & Handle, 10 Amp

Features

- Solid Copper Clip with Insulated Handle
- Banana Plug or Screw Connection
- Overall Length: 2.344" (59.53mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-150-0	Solid Copper Alligator Clip with Barrel, Screw and Black Insulated Handle
72-150-2	Solid Copper Alligator Clip with Barrel, Screw and Red Insulated Handle
72-150-4	Solid Copper Alligator Clip with Barrel, Screw and Yellow Insulated Handle
72-150-5	Solid Copper Alligator Clip with Barrel, Screw and Green Insulated Handle
72-150-6	Solid Copper Alligator Clip with Barrel, Screw and Blue Insulated Handle
72-150-9	Solid Copper Alligator Clip with Barrel, Screw and White Insulated Handle
72-150-KIT	2 Each of 72-150-0 (Black) & 72-150-2 (Red)



Steel Alligator Clip, Insulated, 10 Amp

Features

- Nickel Plated Clip
- Includes Skin Tight Insulation
- Banana Plug or Screw Connection
- Overall Length: 2.125" (53.9mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-158-0	Steel Alligator Clip w/Skin Tight Insulation, Black
72-158-2	Steel Alligator Clip w/Skin Tight Insulation, Red
72-158-KIT	2 Each of 72-158-0 (Black) & 72-158-2 (Red)



Steel Alligator Clip w/Insulated Handle, 10 Amp

Features

- Nickel Plated Clip
- Tenite Acetate Insulated Handle
- Overall Length: 2.234" (56.75mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-185-0	Steel Alligator Clip with Black Insulated Handle
72-185-2	Steel Alligator Clip with Red Insulated Handle



Steel Alligator Clip w/Insulated Grip & Screw, 10 Amp

Features

- Nickel Plated Clip
- PVC Insulated Handle
- Overall Length: 2.480" (62.99mm)
- Jaw Opening: .512" (13.0mm)

	NTE Type No.	Description
NEW	72-189-0	Steel Alligator Clip with Screw & Black Insulated Handle
NEW	72-189-2	Steel Alligator Clip with Screw & Red Insulated Handle




Telecom Clip, Bed of Nails & Single Spike Combo

Features

- Nickel-Silver Jaw Material
- Ideal for Telecom Applications
- Crimp or Solder Connection
- Overall Length: 2.600" (66.0mm)
- Jaw Opening: 1.000" (25.4mm)

NTE Type No.	Description
72-096	Insulator-Piercing Alligator Clip, Glove Style

See page 27 for recommended insulators.



See page 21 for clip & insulator combinations.


Telecom Clip, Bed of Nails & Single Spike Combo

Features

- Nickel-Silver Jaw Material
- Ideal for Telecom Applications
- Crimp or Solder Connection
- Overall Length: 2.600" (66.0mm)
- Jaw Opening: 1.000" (25.4mm)

NTE Type No.	Description
72-167	Insulator-Piercing Alligator Clip, Mitten Style, with Hardware
72-168	Insulator-Piercing Alligator Clip, Mitten Style

See page 26 for recommended insulators.



See page 22 for clip & insulator combinations.