

XPower Inverters - 175 W, 400 W, 700 W



Modified Sine Wave



Mobile Power for Trucks, RVs, Boats and Minivans

By plugging an inverter directly into a 12-volt lighter socket, you can turn your vehicle into a mobile office or have power to run entertainment electronics like popular handheld games or TVs. XPower inverters automatically sense low battery voltage so you never have to worry about a depleted battery. Compact and lightweight, XPower in-vehicle power inverters are available in a variety of power levels.

XPower Inverter 175 Plus

- ▶ 150 watts continuous power with 300 watts surge
- ▶ Automatic shutdown protection against overload, over temperature and low battery conditions
- ▶ Two, three prong grounded AC outlet
- ▶ Quiet operation
- ▶ One year warranty
- ▶ Runs: Cell phone, camcorder, stereo, laptop computer, 13" TV, portable work light

XPower Inverter 400 Plus

- ▶ 320 watts continuous power with 600 watts surge
- ▶ Automatic shutdown protection against overload, over temperature and low battery conditions
- ▶ Two, three prong grounded AC outlets
- ▶ Quiet operation
- ▶ One year warranty
- ▶ Runs: Cell phone, camcorder, stereo, laptop computer, 20" TV/VCR combo, 27" TV

XPower Inverter 700 Plus

- ▶ 560 watts continuous power with 1000 watts surge capacity
- ▶ Automatic shutdown protection against overload, over temperature and low battery conditions
- ▶ DC terminals for direct battery connection
- ▶ Two, three prong grounded AC outlets
- ▶ One year warranty
- ▶ Runs: Cell phone, camcorder, stereo, laptop computer, 27" TV, small power tools and small kitchen appliances

Xantrex Technology Inc.

Headquarters
8999 Nelson Way
Burnaby, British Columbia
Canada V5A 4B5
800 670 0707 Toll Free
604 420 1591 Fax

5916 195th Street NE
Arlington, Washington
USA 98223
800 446 6180 Toll Free
360 925 5144 Fax

xantrex

XPower Inverters - 175 W, 400 W, 700 W

Modified Sine Wave

Electrical Specifications

	175 W	400 W	700 W
Continuous AC output power	150 W	320 W	560 W
5 minutes AC output power	175 W	400 W	700 W
Maximum AC output surge power	300 W	600 W	1000 W
AC output voltage (nominal)	120 VAC	120 VAC	120 VAC
AC output frequency	60 +/- 4 Hz	60 +/- 4 Hz	60 +/- 4 Hz
AC output waveform	Modified sine wave	Modified sine wave	Modified sine wave
Battery drain with no AC load (at 12V input)	0.15 A	0.20 A	0.25 A
Efficiency (maximum)	90%	90%	90%
DC input voltage range	10-15 VDC	10-15 VDC	10-15VDC
Low battery alarm trigger point (nominal)	10.7 V	10.7 V	10.7 V
Low battery shut down point (nominal)	10.0 V	10.0 V	10.0 V
High battery shut down point (nominal)	15.0 V	15.0 V	15.0 V

General Specifications

	175 W	400 W	700 W
Ambient operating temperature range	0°C-40°C (32°F-104°F)	0°C-40°C (32°F-104°F)	0°C-40°C (32°F-104°F)
Dimensions (LxWxH)	5 1/8 x 4 1/8 x 2 1/4" (130x105x56 mm)	5 7/8 x 4 1/8 x 2 1/4" (149x105x56mm)	7 1/4 x 4 1/8 x 2 1/4" (186x105x56mm)
Weight	1 lb 3 oz (550 g)	1 lb 6 oz (655 g)	1 lb 14 oz (900 g)
Warranty	One year	One year	One year
DC connection	Lighter socket	DC socket and hardwire	Hardwire
Part numbers	851-0175	851-0400	851-0700

Note: Specifications subject to change without notice.