



Sample photo

Order symbol: PC 100/60 HG
Product nbr: 6011301

Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074022042
El. number:
Finland 3420311
Denmark 8212022030
Italy 7351025
Sweden 2535512

Including: Base with TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:				Rating:
L	W	H		
mm:	130	80	60	Ingress Protection (EN 60529): IP 66/67
inch:	5.1	3.1	2.4	Impact Resistance (EN 50102): IK 08
Materials:				Electrical insulation: Totally insulated
Material:	PC			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			UV resistance: UL 508
Cover colour:	RAL 7035			Flammability Rating (UL 746 C 5): UL 94 5V
Cover screws material:	Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:	Grey			NEMA Class: NEMA 1, 4, 4X, 6
Gasket material:	TPE			Certificates:
Temperatures:				Germanischer Lloyd (GL)
Short term:	-40 ... 120 °C			Underwriters Laboratories
Continuous:	-40 ... 80 °C			Det Norske Veritas
Short term:	-40 ... 250 °F			Fimko
Continuous:	-40 ... 175 °F			Europe EN 50298 1998
Accessories:				UL Canada
MIV 100	Mounting plate			Gost R
MIN 5	DIN-15 Mounting rail			
MIN 10	DIN-15 Mounting rail			
MIV 5	DIN-35 Mounting rail			
MIV 10	DIN-35 Mounting rail			
FP A 100/130	Front plate			
HFP 130	Front plate hinge series			

