



Contact data 06/1	Conditions	Min	Typ	Max	Unit
Contact - No.				06/1	
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
Switching voltage	DC or Peak AC			200	V
Switching current	DC or Peak AC			0,5	A
Carry current	DC or Peak AC			1	A

Special Product Data	Conditions	Min	Typ	Max	Unit
Number of contacts			1		
Contact - form			A - NO		
Sensor-resistance				460	mOhm
Housing material				PP	
Material of float				PP	
Case colour				white	
Sealing compound				Polyurethan	
Reach / RoHS conformity				yes	

Environmental data	Conditions	Min	Typ	Max	Unit
Shock				50	g
Vibration	from 10 - 1200 Hz			20	g
Operating temperature		-30		70	°C
Operating temperature		-5		70	°C
Storage temperature		-30		70	°C

Cable specification	Conditions	Min	Typ	Max	Unit
Cable type			single wires		
Cable material			PVC		
Cross section			0,25 sq-mm		

General data	Conditions	Min	Typ	Max	Unit
Mounting advice			over 5m cable, a resistor is recommended.		
Tightening torque				0,5	Nm