


# OKARROLL MULTIDIRECTIONAL ROLLERS / TECHNICAL DATA



*DUPLEX ROLLER IN PROFILE*



|   | Ø50  | Ø60  | Ø80  | Ø120  |
|---|------|------|------|-------|
| A | 60.0 | 70.0 | 90.0 | 140.0 |
| B | 56.0 | 68.8 | 78.0 | 113.0 |
| C | 35.0 | 40.0 | 50.0 | 70.0  |

Recommended maximal weight of transported goods.\*

| per roller kg | 10 | 20 | 40 | 200 |
|---------------|----|----|----|-----|
|---------------|----|----|----|-----|

*SIMPLEX ROLLER*

|   | Ø50  | Ø60  | Ø80  | Ø120  |
|---|------|------|------|-------|
| D | 50.0 | 60.0 | 80.0 | 120.0 |
| E | 8.3  | 8.3  | 8.3  | 17.0  |
| F | 19.5 | 25.0 | 30.0 | 39.0  |




*DUPLEX ROLLER*

|   | Ø50  | Ø60  | Ø80  | Ø120 |
|---|------|------|------|------|
| G | 39.0 | 51.0 | 60.0 | 78.0 |

*PROFILES*

|    | Ø50  | Ø60  | Ø80  | Ø120  |
|----|------|------|------|-------|
| H  | 44.0 | 56.0 | 65.0 | 90.0  |
| I  | 42.0 | 47.0 | 60.0 | 90.0  |
| J  | 2.0  | 2.0  | 2.0  | 3.0   |
| L= | 52.0 | 62.0 | 82.0 | 100.0 |
| L= | 1000 | 1000 | 1000 |       |



\* Depends on roller distance and quality of surface of plate.

Manufacturer:

## OKARTEK

Leipurinkatu 5, FI-20780 Kaarina, FINLAND  
tel. +358 2 273 9400, fax. +358 2 273 9460  
[www.okartek.fi](http://www.okartek.fi)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Parallax:

730-00054