




TOLERANCE  $\pm .010$

COIL: @  $25^{\circ} \text{ C}$   
 RESISTANCE 540-770 OHMS  
 NOMINAL VOLTAGE 26.5 VDC  
 MUST OPERATE 13.0 VDC  
 MUST RELEASE 10.1 VDC MAX, 2.3 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 MS. DURATION


TEMPERATURE -65  $^{\circ} \text{ C}$  TO +125  $^{\circ} \text{ C}$

NOTES: OPERATE & RELEASE TIME 6 MS MAX.

\* CONTACT BOUNCE 1 MS MAX.

\* (MEASURED AT 100mA 28 VDC)

CUSTOMER DATA SHEET



CONTACT RATING: 2 AMPS 28 VDC  
RESISTIVE 100,000 OPERATIONS

DR. R.B. 11/15/95 CK. 11/15/95 MB

**COMMUNICATIONS  
INSTRUMENTS, INC.**

CUST. QPL  
 CUST. NO M5757/10-039

TYPE "FW" RELAY

**FW1120G01**