


## ENERGIZER 10 size - **Mercury Free**

## ZnAir



(top view) (bottom view)

### Industry Standard Dimensions




### Specifications

|                          |                                                            |
|--------------------------|------------------------------------------------------------|
| <b>Chemical System:</b>  | Zinc Air (Zn/O <sub>2</sub> )                              |
| <b>Tab Color:</b>        | Yellow                                                     |
| <b>Designation:</b>      | ANSI-7005ZD, IEC-PR70                                      |
| <b>Nominal Voltage:</b>  | 1.4 Volts                                                  |
| <b>Typical Capacity:</b> | 91 mAh (to 0.9 volts)<br>(Rated at 3k ohms at 21°C/50% RH) |
| <b>Typical Weight:</b>   | 0.32 grams (0.01 oz.)                                      |
| <b>Typical Volume:</b>   | 0.08 cubic centimeters (0.005 cubic inch)                  |


### Typical Discharge Characteristics

IEC Industry Standards / Standard Test Protocol  
(3/.7 mA .1S/1H59M 59.9S 12H at 21C)




### Typical Discharge Characteristics

ANSI/IEC Industry Standards / Intermittent Test Protocol  
(3K ohm 12 hours per day at 21C)



### Typical Discharge Characteristics

IEC Industry Standards / High Drain Test Protocol  
(5/1 mA .1S/1H59M 59.9S 12H at 21C)



### Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.  
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.