




CK23M

Fast response contact surface probe, 90 degree angle swivel head sensor



Copyright © 2007 Test Products International, Inc.

Application	Range°F°C	Probe tip	Dimensions	Insulation Material
Contact temperatures on flat and uneven surfaces	-58° to 932°F -50° to 500°C	32	Stem Length: 4.9" (125mm) w/90° bend Diameter: 0.6" (15mm) Lead Length: 39.4" (1M)	Polyurethane