

Quick Links
RoHS/LF P/N Search
Documentation
Customer drawing search
Free search
Services
Distributor list

Start > Search=54241001* > 54241001

54241001

54241001 : 10 way Male Key B Slot 1



ACTIVE

RoHS Compliant

[Add to Favorites](#)[Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)[Sample request](#)[Customer drawing](#)[Specifications](#)[Download document](#)[Mating Half](#)

General	Mechanical	Physical	Terminal 1 Type	Environmental	Other Features
General					
Application					Wire to Wire Harness in-line
Ways					10
Coding version					B
Product Type					Housing
Coding					Yes
Features					Mechanical polarization Circumferential interface seal Terminal position assurance (T.P.A.) Several colour codings available Rear sealing ensured by a pre-mounted grommet Suitable for engine compartment applications Clip Slot 1 High Performance APEX technology
Hybrid					No
Main Terminal family					APEX 150
Main Terminal size					1.5 mm
Sealed					Yes
Terminal Size					1.5
Mechanical					
Connector mating force					< 75N
Physical					
Color					Grey
Material					PBT
Temperature (Range)					-40°C to +125°C
Terminal 1 Type					
Terminal type 1					APEX Male 150 Terminal
Ways for Terminal Type 1					10
Contact insertion force for Terminal Type 1					15N
Contact Pitch for Terminal Type 1					3.5x6 mm
Retention force (Contact) for Terminal Type 1					> 90N
Environmental					
IMDS					Yes
Other Features					
Market					Passenger Vehicles
Type					Male
Part Situation					Active
Disclaimer					For more information, please contact your local sales office. Displayed data is for information purposes only The supply of some products might be limited to some customers