



- NOTES: 1. MEASURED AT THE BOTTOM
2. MATERIAL: GLASSREINFORCED POLYESTER UL94 - V0
3. THE "LF" PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS 22-008.
4. PARTS WITH AND WITHOUT SUFFIX LF TO THE PRODUCT PART NUMBER ARE IDENTICAL IN FORM, FIT AND FUNCTION. LF SUFFIX IS ADDED TO THE PART NUMBER OF THIS PRODUCT TO HAVE UNIFORM IDENTIFICATION OF ALL RoHS COMPATIBLE PRODUCTS.

ABRIDGED  
CAT No MARKED




RoHS COMPATIBLE  
(DIGIT 11&12)

HM2H87P1-LF

STANDOFF HEIGHT INDICATOR

| PART NUMBER  | L1  | L2    |           |
|--------------|-----|-------|-----------|
| HM2H87P1LF   | 3.0 | 13.45 | AVAILABLE |
| HM2H87P109LF | 3.9 | 14.35 | AVAILABLE |
| HM2H87P115LF | 4.5 | 14.95 | AVAILABLE |
| HM2H87P117LF | 4.7 | 15.15 | AVAILABLE |
| HM2H87P119LF | 4.9 | 15.35 | AVAILABLE |



1DEC ±0.2  
2DEC ±0.1  
ANGLES ±1°

WE RESERVE THE RIGHT TO CHANGE  
DIMENSIONS OR REQUIREMENTS  
WITHOUT PRIOR NOTICE.

ALL DIMENSIONS IN MM

| APPR.         | DATE       | SIGN.   |
|---------------|------------|---------|
| DRAFT         | 1997-05-12 | M. FRET |
| CHECKED       |            |         |
| PROD. MGR.    |            |         |
| PR. ENG. MGR. |            |         |
| PR. MGT. MGR. |            |         |

REFERENCES

MPACS 8+2R SHROUD TYPE D

CAT. No. HM2H87P1--LF

FCI www.fciconnect.com

SCALE  
3/1

BS,C ,202311,005

D

THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED  
OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT  
OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

DIT IS ONZE EIGENDOM EN MAG NIET NAGEMAAKT, HERDRUKT, OVERGEHAAKT AAN  
DEREN, NOCH VOOR FABRICATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE  
TOELATING. BIJ NIET GEBRUIK IS TERUGGEGANG VERPLICHT.



PDM: Rev:D

STATUS: Released

CUSTOMER DRAWING REVISION  
Printed: Dec 03, 2007