



T-2 Wire Terminal (short)




Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
CM4ES	4.0	.040	200	10,000	C-6
CM5ES	5.0	.040	225	8,000	C-6
CM6ES	6.0	.040	250	10,000	C-2V
CM10AS	10.0	.010	RED GLOW	50,000	C-2F
CM10CS	10.0	.017	60	20,000	C-2V
CM10ES	10.0	.035	450	1,000	C-6
CM12ES	12.0	.040	650	7,500	C-2V
CM16CS	16.0	.017	80	15,000	C-2F
CM16ES	16.0	.040	800	7,500	C-2F
CM18ES	18.0	.040	850	5,000	C-2F
CM24CS	24.0	.017	100	15,000	C-2F
CM24ES	24.0	.040	850	8,000	C-2F
CM28ES	28.0	.040	1,500	6,000	C-2F
CM48ES	48.0	.040	3,000	5,000	CC-2F

T-2 Wire Terminal (standard)



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
CM6PS	6.0	.140	550	20,000	C-2V
CM12PS	12.0	.170	2,000	12,000	C-2F
CM24PS	24.0	.073	3,000	10,000	C-2F
CM28PS	28.0	.040	1,600	5,000	C-2F
CM48PS	48.0	.053	1,800	10,000	C-7A
CM60PS	60.0	.050	2,200	7,500	C-7A
CM120PS	120.0	.025	1,200	5,000	CC-7A

T-2 Telephone Slide Base - Type 5 (short)



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
CM4ESB	4.0	.040	200	10,000	C-6
CM5ESB	5.0	.040	225	8,000	C-6
CM5SLB	5.0	.120	1,600	2,500	C-2V
CM6ESB	6.0	.040	250	10,000	C-2V
CM10ASB	10.0	.010	-	50,000	C-2F
CM10CSB	10.0	.017	60	20,000	C-2V
CM10ESB	10.0	.035	450	1,000	C-6
CM12ESB	12.0	.040	650	7,500	C-2V
CM14FSB	14.0	.080	4,000	500	C-2F
CM16CSB	16.0	.017	80	15,000	C-2F
CM16ESB	16.0	.040	800	7,500	C-2F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

VCC:

[120PS](#) [48PS](#) [10AS](#) [28ES](#) [12PS](#) [12ES](#) [16ES](#)