



HIGH-PERFORMANCE LED SOLDERING IRONS

HEAVY DUTY



80-WATT LED SOLDERING IRON



Three 5mm high-temperature, long-life LEDs at 25 lumens/ft² for superior soldering accuracy and application illumination

Co-molded, soft-grip ribbed handle design for maximum comfort and reduced slippage

Triangular area for maximum of tip control and round handle for ease of tip rotation

High-performance, stainless-steel heater technology with heat up to 950°F

A 7-year warranty, longest in the industry

Cord strain relief for extended life

Possible applications: audio systems, electrical grounding, automotive, marine, jewelry, wire connection <4 AWG (0.20" diameter)

UL Listed – cUL available

IMPORTANT: use only Weller® tips



PRODUCT DETAILS

Catalog number:	SP80NUS
UPC number:	03703266941
Type:	Non-temperature controlled
Wattage:	80W
Temperature:	900° F / 482° C
Cord length:	5 feet
Iron tip:	MTG20, chisel, 0.375"
Package includes:	Peg hook, retail packaging, iron stand, user manual
Compatible tips:	MTG21, chisel, 0.250" MTG22, conical, 0.375"
Stock item:	Normal stock item
Packaging (LxWxH):	12.37" x 4.87" x 1.76"
Gross weight:	0.466 lbs.

A family of wattages: **15** **25** **40** **80** Find your favorite.

